


DURB1640CT




Description

Littelfuse DUR series Ultrafast Recovery Rectifier is designed to meet the general requirements of commercial applications by providing low T_{rr} , high-temperature, low-leakage and low forward voltage drop products. It is suitable for output rectifier, free-wheeling or boost diode in high-frequency power switching application such as switch mode power supply and DC-DC converters.

Features

- Ultra-fast switching
 - Low reverse leakage current
 - High surge current capability
 - Low forward voltage drop
 - Common cathode
- configuration in surface mount TO-263 (D²PAK) package
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/JEDEC J-STD-609A.01)

Circuit Diagram



Applications

- Output rectifiers in switch mode power supplies (SMPS) and DC to DC converters
- Free-wheeling diode or boost diode in converters and motor control circuits
- Anti-parallel diode for high frequency switching devices such as IGBT
- Uninterruptible Power Supplies (UPS)
- Inductive heating and melting
- Ultrasonic cleaners and welders

Maximum Ratings

Characteristics	Symbol	Conditions	Max.	Unit
Peak Inverse Voltage	V_{RWM}	-	400	V
Average Forward Current	$I_{F(AV)}$	50% duty cycle @ $T_c = 105^\circ\text{C}$, rectangular wave form	8 (Per Leg) 16 (Total Device)	A
Peak One Cycle Non-Repetitive Surge Current (per leg)	I_{FSM}	8.3 ms, half sine pulse	80	A

Electrical Characteristics

Characteristics	Symbol	Conditions	Max.	Unit
Forward Voltage Drop (Per Leg) ¹	V_{F1}	@8A, Pulse, $T_j = 25^\circ\text{C}$	1.3	V
	V_{F2}	@8A, Pulse, $T_j = 125^\circ\text{C}$	1.2	V
Reverse Current	I_{R1}	@ V_R = Rated V_R , $T_j = 25^\circ\text{C}$	10	μA
	I_{R2}	@ V_R = Rated V_R , $T_j = 125^\circ\text{C}$	500	μA
Reverse Recovery Time	t_{rr1}	$I_F = 500\text{mA}$, $I_R = 1\text{A}$, and $I_{rm} = 250\text{mA}$	45	ns

Footnote 1: Pulse Width < 300 μs , Duty Cycle < 2%

Thermal-Mechanical Specifications

Characteristics	Symbol	Conditions	Specification	Unit
Junction Temperature	T_J	-	-55 to +150	°C
Storage Temperature	T_{stg}	-	-55 to +150	°C
Typical Thermal Resistance Junction to Case	$R_{\theta JC}$	DC operation	5.0	°C/W
Approximate Weight	wt	-	1.41	g
Case Style	-	D ² PAK	-	-

Figure 1: Typical Forward Characteristics




Figure 2: Typical Reverse Characteristics






Figure 3: Typical Junction Capacitance



Part Numbering and Marking System




Ultrafast Recovery Rectifier

DURB1640CT, 2x 8A, 400V, TO-263, Common Cathode

Packing Options

Part Number	Marking	Packing Mode	M.O.Q
DURB1640CT	DURB1640CT	800pcs / reel	800


Dimensions-Package TO-263 (D²PAK)



	Millimeters	
	Min	Max
A	4.06	4.83
A1	0.00	0.25
b	0.51	0.99
b1	1.14	1.78
c	0.31*	0.74
c1	1.14	1.65
D	8.38	9.65
D1	6.40*	-
E	9.65	10.67
E1	6.22	-
E2	9.65	10.67
e	2.54 BSC	
H	14.60*	15.88
L	1.78	2.79
L1	-	1.68
L2	-	1.78
L3	0.254 BSC	

Footnote *: The spec. does not comply with JEDEC spec.

Carrier Tape & Reel Specification TO-263 (D²PAK)



	Millimeters	
	Min	Max
A	10.70	10.90
B	16.03	16.23
C	5.11	5.31
d	ø1.45	ø1.65
E	1.65	1.85
F	11.40	11.60
P0	3.90	4.10
p	15.90	16.10
P1	1.90	2.10
W	23.90	24.30