




RESISTANCE @ +25°C = 10,000 Ω NOMINAL
 ACCURACY (0 TO +50°C) = $\pm 0.10^\circ\text{C}$
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = $-4.4\%/^\circ\text{C}$ NOMINAL
 MAXIMUM TEMPERATURE RATING = +105°C

MAXIMUM TEMPERATURE FOR BEST LONG-TERM STABILITY = +75°C

LEAD WIRE: 30 AWG (0.010" DIAMETER), TWO CONDUCTOR,
 SOLID CONDUCTOR, PVC INSULATED

*** ROHS COMPLIANT ***

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	05/22/13	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT U.S. SENSOR CORP.	
DRAWN BY	DAN DANKERT		
DATE	05/22/13	714-639-1000 www.ussensor.com	
REV	NONE	THERMISTOR PROBE	
LAYER	0 OF 2	P/N USP14439	