





RESISTANCE @ +25°C = 1,000 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "B"
 BETA " β " (0 TO +50°C) = 2,941°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -3.3%/°C NOMINAL
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL
 MAXIMUM TEMPERATURE RATING = +220°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	03/28/03	DD
"A"	LENGTH WAS 0.155" $\pm$ 0.010" & TAB THICKNESS WAS 0.019" $\pm$ 0.005"	03/28/03	DD

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC THERMISTOR P/N SM102B1K
DRAWN BY DAN DANKERT	
DATE 03/28/02	
REV. "A"	
LAYER 0 OF 2	