




RESISTANCE @ +25°C = 10,000 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +150°C

---	ISO RELEASE	04/17/03	DD
"A"	ADDED LEAD ELECTRICALLY CONNECTED TO MOUNTING TAB NOTE	12/17/02	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	11/15/99	
REV.	"A"	
LAYER	0 OF 1	
		TO-220 THERMISTOR PROBE
		P/N TO103J2K