





RESISTANCE @ +25°C = 100,000 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 5 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = +220°C

---	ISO RELEASE	11/03/11	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC THERMISTOR P/N MM104J1K
DRAWN BY	DAN DANKERT	
DATE	02/11/02	
REV.	NONE	
LAYER	0 OF 1	