




RESISTANCE @ +25°C = 100 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "B"  
 TEMPERATURE COEFFICIENT @ +25°C = -3.31%/°C NOMINAL  
 BETA "β" (0 TO +50°C) = 2,941°K NOMINAL  
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)  
 THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +100°C

| REV  | REVISION RECORD       | DATE     | APP |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 05/01/03 | DD  |
|      |                       |          |     |

|          |             |                               |  |
|----------|-------------|-------------------------------|--|
| SCALE    | NONE        | © COPYRIGHT                   |  |
| DRAWN BY | DAN DANKERT | U.S. SENSOR CORP.             |  |
| DATE     | 05/01/03    | 714-639-1000 www.ussensor.com |  |
| REV      | NONE        | NTC THERMISTOR                |  |
| LAYER    | 0 OF 1      | P/N TC101B2K                  |  |