




RESISTANCE @ +25°C = 10,000 Ω ± 1%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 MAXIMUM TEMPERATURE RATING = +125°C

MAXIMUM TEMPERATURE FOR BEST LONG-TERM STABILITY = +100°C

LEAD WIRE: 38 AWG (0.004" DIAMETER), TWO CONDUCTOR,  
 SOLID CONDUCTOR, POLY-NYLON INSULATED

\*\*\* ROHS COMPLIANT \*\*\*

SEE MANUFACTURING SPECIFICATION (LAYER 1)

|      |                       |          |     |
|------|-----------------------|----------|-----|
|      |                       |          |     |
| NONE | RELEASE TO PRODUCTION | 01/11/12 | DD  |
| REV  | REVISION RECORD       | DATE     | APP |

|          |             |                               |  |
|----------|-------------|-------------------------------|--|
| SCALE    | NONE        | © COPYRIGHT                   |  |
| DRAWN BY | DAN DANKERT | U.S. SENSOR CORP.             |  |
| DATE     | 01/11/12    | 714-639-1000 www.ussensor.com |  |
| REV      | NONE        | THERMISTOR PROBE              |  |
| LAYER    | 0 OF 2      | P/N USP12837                  |  |