# Axial Lead & Cartridge Fuses 2AG > Fast Acting > 224/225 Series

# 224/225 Series Lead-Free 2AG, Fast-Acting





#### Agency Approvals

Agency	Agency File Number	Ampere Range
(l)	E10480	0.375A - 3.5A
74	E10480	4A - 10A
<b>⊕</b> .	29862	0.375A - 10A
⟨PS⟩	225 (Cartridge Version) NBK200405-E10480A NBK200405-E10480C NBK110512-E10480A NBK190619-E10480A	1A 1.5A - 3.5A 4A - 5A 6A - 10A
E	224 (Axial Leaded Version) NBK200405-E10480B NBK200405-E10480D NBK110512-E10480B NBK190619-E10480B	1A 1.5A - 3.5A 4A - 5A 6A - 10A
Œ	N/A	0.375A - 10A

### **Electrical Characteristics for Series**

% of Ampere Rating	Opening Time
100%	4 hours, Minimum
135%	1 hour, Maximum
200%	1 sec., Maximum

# Description

The 2AG Fast-Acting Fuses are available in cartridge form or with axial leads. 2AG Fuses provide the same performance characteristics as their 3AG counterpart, while occupying one-third the space. Sleeved fuses are available.

#### **Features**

- In accordance with Underwriter's Laboratories Standard UL/CSA/NMX 248-14
- Available in cartridge and axial lead form and
- with various forming dimensions
- RoHS compliant and Lead-free

#### **Applications**

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

# **Additional Information**



Resources 224 Series



Resources 225 Series



Samples 224 Series



Samples 225 Series



Accessories 224 & 225 Series

For recommended fuse accessories for this product series, see ' $\underline{\text{Recommended Accessories}}\text{'} \text{ section}.$ 

# **Electrical Characteristic Specifications by Item**


	Ampere	Voltage	Interrupting Nominal Cold Resistance (Ohms)	Nominal Cold	Nominal	Agency Approvals				
Amp Code	•	Rating (V)			(I)	71	<b>⑤</b>	PS E	Œ	
.375	0.375	250	35A@250Vac	0.3950	0.171	X		Х		X
.500	0.5	250	10KA@125Vac	0.2650	0.365	X		X		X
.750	0.75	250	10KA@125Vdc 10KA@125Vdc	0.1520	1.050	X		X		X
001.	1	250		0.1027	2.220	X		X	X	X
01.5	1.5	250		0.0712	0.800	X		X	X	X
002.	2	250	100A@250Vac	0.0497	2.180	X		X	X	X
02.5	2.5	250	10KA@125Vac	0.0372	3.820	X		X	X	X
003.	3	250	10KA@125Vdc	0.0317	4.620	X		X	X	X
03.5	3.5	250		0.0265	6.700	X		X	X	X
004.	4	125	100A@250Vac	0.0240	9.400		X	X	X	X
005.	5	125	500A@125Vac	0.0186	17.0		X	X	X	X
005.	5	250	500A@125VaC	0.0186	17.0		X	X		X
006.	6	125	500A@125Vac	0.0154	22.1		X	X	X	X
007.	7	125		0.0130	40.0		X	X	X	X
008.	8	125		0.0107	56.0		X	X	X	X
010.	10	125		0.0075	116.0		X	Х	X	X

<sup>\* 10</sup>A with 500A @ 125 Vdc internal breaking capacity testing

<sup>\*\*:</sup> Interrupting Rating may differ based on Agency Approval. See Agency Approval certificate for more details...




# **Temperature Re-rating Curve**




#### Note:

Rerating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

# **Average Time Current Curves**



# **Soldering Parameters - Wave Soldering**



# **Recommended Process Parameters:**

Wave Parameter	Lead-Free Recommendation		
Preheat: (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)		
Temperature Minimum:	100°C		
Temperature Maximum:	150°C		
Preheat Time:	60-180 seconds		
Solder Pot Temperature:	260°C Maximum		
Solder Dwell Time:	2-5 seconds		

# **Recommended Hand-Solder Parameters:**

Solder Iron Temperature: 350°C +/- 5°C Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

# Axial Lead & Cartridge Fuses 2AG > Fast Acting > 224/225 Series


# **Product Characteristics**


Materials	Body: Glass Cap: Nickel-plated brass Leads: Tin-plated Copper
Terminal Strength	MIL-STD-202, Method 211, Test Condition A
Solderability	MIL-STD-202 Method 208
Product Marking	Cap1 : Brand logo, current and voltage ratings Cap2 : Series and agency approval marks

Operating Temperature:	−55°C to 125°C.
Thermal Shock:	MIL-STD-202, Method 107, Test Condition B (5 Cycles -65°C to +125°C).
Vibration	MIL-STD-202, Method 201
Humidity	MIL-STD-202, Method 103, Test Condition A: High RH (95%) and elevated temp (40°C) for 240 hours
Salt Spray	MIL-STD-202, Method 101, Test Condition B

#### **Dimensions**

# **Part Numbering System**





# **Packaging**

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width		
		224 Series				
Bulk	N/A	1000	MX	N/A		
Bulk	N/A	100	HX	N/A		
Reel and Tape	EIA 296-E	1500	DRT1	T1=53mm (2.087")		
225 Series						
Bulk	N/A	1000	MX	N/A		
Bulk	N/A	100	HX	N/A		

#### **Recommended Accessories**

Accessory Type	Series	Description	Max Application Voltage	Max Application Amperage
	<u>245</u>	Panel Mount Shock-Safe Fuseholder	300	10
Holder	<u>150</u>	In-Line Fuseholder	350	10
	286	Panel Mount Flip-Top Shock-Safe Fuseholder	250	10
Block	254	OMNI-BLOK® Fuse Block	400	10
Clip	<u>111</u>	PC Board Mount Fuse Clip	250	10

#### Notes:

- 1. Do not use in applications above rating.
- 2. Please refer to fuseholder data sheet for specific re-rating information.
- 3. Please contact factory for applications greater than the max voltage and amperage shown.