Blade Fuses





MAXI Blade Fuses Rated 58V

The MAXI® style fuse for use in 42V Systems. Same Time-Current characteristic as the 32V MAXI fuse using "Diffusion Pill Technology" to provide predictable time delay characteristics and low heat dissipation. Fits into standard MAXI® fuse sockets. Has a rejection feature to prevent fuses with lower voltage rating from being wrongfully inserted into the circuit. Current rating 20A - 80A @58 VDC max.

58 VDC

Specifications


Voltage Rating:
Interrupting Rating:
*Recommended Environmental Temperature:
Terminals Material:
Housing Material:
Net Weight Per Fuse:
Complies with:

1000A @ 58 VDC -40°C to +125°C Silver plated zinc alloy PA66 (U.L. 94 Flammability rating — V2) 5.7±5% gr SAE J 1888, SAE 2576 ISO 8820-3:2002(E)



^{*}Silver plating allows up to 150°C at the terminal interface.

Time-Current Characteristic Curves



Ordering Information

Part Number	Rating	Package Size		
0999xxx.ZXN	20 - 80	1200		

Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)		
110	360,000 /∞		
135	60 / 1,800		
200	2 / 60		
350	0.2 / 7		
600	0.04 / 1		

Ratings

Part Number	Current Rating (A)	Housing Material Color	Test Cable Size (mm²)	Typ. Voltage Drop (mV)	Typ. Cold Resistance (m Ω)	Typ. I²t (A²s)
0999020	20		4	76	3.10	1,100
0999025	25		4	75	2.39	2,100
0999030	30		4	77	1.95	4,070
0999035	35		4	75	1.71	6,00
0999040	40		4	75	1.42	8,500
0999050	50		6	73	1.10	11,300
0999060	60		6	77	0.89	15,300
0999070	70		10	61	0.64	21,200
0999080	80		10	62	0.54	43,600

REV0727202

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-saving, life-saving or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

Blade Fuses




MAXI Blade Fuses Rated 58V

Dimensions

Dimensions in mm for reference only. See outline drawing for dimensions and tolerances.






Temperature Table

	max. allowed current load [A] at ambient temperature (typical derating)						
	-40°C	0°C	20°C	65°C	85°C	110°C	125°C
20A	20	20	20	20	18	15	13
25A	25	25	25	23	21	18	15
30A	30	30	30	28	25	21	18
35A	35	35	35	30	27	23	19
40A	40	40	40	34	30	25	22
50A	50	50	50	42	38	31	27
60A	60	60	56	47	42	35	31
70A	70	70	68	57	51	43	37
80A	80	78	74	62	56	47	40

Typical Derating of Fuse Melting Element

Temperature Security Margin is 20% Please Contact Littelfuse® for Details Regarding Derating Test Set-Up.



Derating curves may change depending on the final condition of the application (terminals characteristics, wire size etc...). Please ask Littelfuse® for more information.

REV0727202