461 Series TeleLink® Fuse

Surge Resistant





Additional Information







Resources

Accessories

Samples

Agency Approvals

Agency	Agency File Number	Ampere Range
<i>71</i> 2	E10480	0.5A - 2A
® .	29862	0.5A - 2A
\triangle	J50502555	0.5A - 2A

Electrical Characteristics for Series

% of Ampere Rating	Opening Time
100%	4 hours, Minimum
250%	1 sec., Minimum; 120 secs., Maximum

Maximum Temperature Rise

Telecom Nano ^{2®} Fuse	Temperature Reading
04611.25	< 82°C (180°F)
0461002.	< 50°C (122°F)

Higher Currents and PCB layout designs can affect this parameter. Readings are measured at rated current after temperature stabilizes

Description

The Littelfuse 461 Series TeleLink® Surface Mount, Surge Resistant Fuse, offers over-current protection for a wide range of telecom applications without requiring a series resistor. When used in conjunction with a Littelfuse SIDACtor® Transient Voltage Suppressor (TVS) or a GreentubeTM Gas Plasma Arrestor, this combination provides a compliant solution for standards and recommendations such as GR-1089–Core, TIA-968-A, UL/EN/IEC 60950, and ITU K.20 and K.21. The coordination requirement contained in GR-1089–Core, and ITU K.20/21 may require a series of impedance devices.

Features & Benefits

- Surface mount surge resistant
 2A rating has improved Slo-Blo® fuse
 temperature rise perform
- Meet UL 60950 3rd Edition power cross requirements standard alone
- Designed to allow compliance with Telcordia GR-1089-CORE and TIA-968-A (formerly FCC Part 68) Surge Specifications
 Product is Halogen Free and RoHS compliant and compatible with lead-free solder and higher temperature.
- Provide coordinated protection with Littelfuse SIDACtor®
 Transient Voltage Suppressor (TVS)or a GreentubeTM Gas Plasma Arrestor, without series resistors
- Designed to serve the requirements of a wide range of telecommunication and networking equipment

- 2A rating has improved temperature rise performance under 2.2A surge current testing when compared with 1.25A rating
- Product is Halogen Free and RoHS compliant and compatible with lead-free solder and higher temperature profiles when ordered with Standard Silver Plated Brass Caps
- UL Recognized to UL/CSA/ NMX 248-1 and UL/CSA/NMX 248-14
- Conforms to IEC/EN 60127-1 and IEC/EN 60127-7

Applications

- T1/E1/J1 and HDSL2/4
- SLIC interface portion of Fiber to the Curb (FTTC) and Fiber to the Premises (FTTP)
- Non-Fiber SLIC interface for Central Office (CO) locations and Remote Terminals (RT)
- xDSL applications such as ADSL, ADSL2+, VDSL, and VDSL2+
- Ethernet 10/100/1000BaseT
- POTS applications such as modems, answering machines, telephones, fax machines, and security systems
- ISDN "U" interface
- Baystation T1/E1/J1, T3 (DS3) trunk cards



461 Series TeleLink® Fuse Surge Resistant


Electrical Specifications by Item

Ampere		Max Voltage	Interrupting	terrupting Nominal Cold		Age	ncy Appro	vals
Rating (A)	Amp Code	Rating (V)	Rating ²	Resistance (Ohms)	Nominal Melting I²t (A²sec)	<i>71</i>	⊕ ;	\triangle
0.500	.500	600	50A @ 250 VAC	0.560	0.840 ¹	X	X	X
1.25	1.25	600	60 A @600 VAC	.1040	16.5 ¹	X	X	X
2.00	002.	600	100 A @80 VDC	.0450	17.5 ¹	X	X	X

¹ I²t is calculated at 10 msecs. or less. I²t at 10 times rated current has a typical value of: 24 A²sec (2.0A), 22 A²sec (1.25A), 1.3 A²sec (0.5A).


- Typical inductance <40nH up to 500 MHz.
- Resistance changes 0.5% for every °C.
- Resistance is measured at 10% rated current.

Temperature Re-rating Curve



Note:

Average Time Current Curves



GR 1089 Inter-building requirements

GR 1089 1st level lighting surge inter-building

(Equipment under test can not be damaged and must continue to operate properly)

Surge	Minimum Peak Voltage (V)	Minimum Peak Current (A)	Max. Rise/Min. Decay (µs)	Repetitions Each Polarity	Fuse Choices
1	600	100	10/1000	25	1.25, 2.0
2	1000	100	10/360	25	1.25, 2.0
3	1000	100	10/1000	25	1.25, 2.0
4	2500	500	2/10	10	1.25, 2.0
5	1000	25	10/360	5	0.5, 1.25, 2.0

If sufficient series resistance is used, then the 0.5 fuse may be used in test conditions 1-4.

GR 1089 2nd level lightning surge telecom port

(Equipment under test shall not become a fire or electrical safety hazard)

Surge	Minimum Peak Voltage (V)	Minimum Peak Current (A)	Max. Rise/Min. Decay (μs)	Repe-titions Each Polarity	Fuse Choices
1	5000	500	2/10	1	0.5, 1.25, 2.0
Alter-native	5000	500/8=625	8/10	1	0.5, 1.25, 2.0

The 0.5 fuse will open during these test conditions. The 1.25 & 2.0 will not open thus providing operational compliance.



²Interrupting Rating may differ based on Agency Approval. See Agency Approval certificate for more details.

Re-rating depicted in this curve is in addition to the standard re-rating of 25% for continuous operation.

461 Series TeleLink® Fuse Surge Resistant

GR 1089 AC power fault 1st level inter-building

(fuse not allowed to open)

Test	Vrms	Short Circuit Current (A)	Hits	Duration	Primary Protector	Fuse Choices
1	50	0.33	1	15 min.	removed	1.25, 2.0
2	100	0.17	1	15 min.	removed	1.25, 2.0
3	200,400, 600	1	60	1 sec.	removed	1.25, 2.0
4	1000	1	60	1 sec.	operative	1.25, 2.0
5	Diagram	Diagram	60	5 secs.	removed	1.25, 2.0
6	600	0.5	1	30 secs.	removed	1.25, 2.0
7	440	2.2	5	2 secs.	removed	1.25, 2.0
8	600	3	1	1.1 secs.	removed	1.25, 2.0
9	1000	5	1	0.4 sec.	in place	1.25, 2.0

GR 1089 AC power fault 2nd level (fuse can open but must open in a safe and controlled manner)

Test Circuit	Vrms	ShortCircuit Current(A)	Duration	Fuse
1	120,277	25	15 min.	0.5, 1.25, 2.0
2	600	60	5 secs.	0.5, 1.25, 2.0
3	600	7	5 secs.	0.5, 1.25, 2.0
4	100-600	2.2	15 min	0.5, 1.25, 2.0
5	Diagram	Diagram	15 min.	0.5, 1.25, 2.0

Fuse must open before wiring simulator fuse (MDL 2.0).

TIA -968-A (formerly FCC Part 68) Surge Waveforms (fuse can not open during type B events)

Surge	Voltage (V)	Waveform (µs)	Current (A)	Repetitions	Recommended Fuse
Metallic A	800	10×560	100	1 ea. polarity	1.25
Longitudinal A	1500	10×160	200	1 ea. polarity	1.25
Metallic B	1000	9×720	25	1 ea. polarity	1.25
Longitudinal B	1500	9×720	37.5	1 ea. polarity	1.25

For the type A events the 0.5 fuse will open, providing non-operational compliance. The 1.25 & 2.0 will not open, providing for operational compliance with TIA-968-A type A surge events.

UL 60950 requirements

UL60950 (EN 60950) (formerly UL 1950) Power Cross


(L = Iongitudinal, M = metallic)

Test Number	Voltage (V)	Current (A)	Time	Fuse Choices
L1	600	40	1.5 secs.	0.5, 1.25, 2.0
L2	600	7	5 secs.	0.5, 1.25, 2.0
L3	600	2.2	30 min.	0.5, 1.25, 2.0
L4	200	2.2	30 min.	0.5, 1.25, 2.0
L5	120	25	30 min.	0.5, 1.25, 2.0
M1	600	40	1.5 secs.	0.5, 1.25, 2.0
M2	600	7	5 secs.	0.5, 1.25, 2.0
M3	600	2.2	30 min.	0.5, 1.25, 2.0
M4	600	2.2	30 min.	0.5, 1.25, 2.0

Selection of test number depends on current limiting F fire enclosure/spacing of end product

- 26 AWG line cord removes L1/M1 test requirement
- L5 conducted only if product does not pass section 6.1.2
- L2,M2,L3,M3,L4,M4 conducted if not in a fire enclosure Fuse must open before the wiring simulator fuse (MDL 2.0).

Dimensions



UL60950 (EN 60950) (formerly UL 1950) Impulse Test and Steady-State Electric Strength Test


Test	Voltage (V)	Current (A)	Waveform	Repetitions	Fuse Choices
		lmp	ulse		
For handheld units	2500	62.5	10×700ms	+/- 10 w/60 secs. rest	0.5, 1.25, 2.0
Non handheld	1500	37.5	10×700ms	+/- 10 w/60 secs. rest	0.5, 1.25, 2.0
		Steady	y-State		
For handheld units	1500		60Hz		0.5, 1.25, 2.0
Non handheld	1000		60Hz		0.5, 1.25, 2.0



461 Series TeleLink® FuseSurge Resistant

Soldering Parameters


Reflow Cond	Pb – free assembly		
	-Temperature Min (T _{s(min)})	150°C	
Pre Heat	-Temperature Max (T _{s(max)})	200°C	
	-Time (Min to Max) (t _s)	60 - 180 seconds	
Average Ran	Average Ramp-up Rate (Liquidus Temp (T _L) to peak)		
$T_{\text{S(max)}}$ to T_{L} -	T _{S(max)} to T _L - Ramp-up Rate		
Reflow	- Temperature (T _L) (Liquidus)	217°C	
nellow	-Temperature (t _L)	60 – 150 seconds	
Peak Temper	rature (T _P)	260 ^{+0/-5} °C	
Time within	5°C of actual peak Temperature (t _p)	20 - 40 seconds	
Ramp-down	6°C/second max.		
Time 25°C to	8 minutes max.		
Do not exce	ed	260°C	



Product Characteristics

Materials	Body: Ceramic Terminations: Silver-plated Caps		
Product Marking	Brand Logo, Ampere Rating, T		
Operating Temperature	-55°C to 125°C		
Moisture Sensitivity Level	Level 1, J-STD-020		
Solderability	IEC 60127-4 (215°C immersion, 3 seconds)		
Resistance to Dissolution of Metallization	IPC / EIA J-STD-002-Test D 260°C for 120 seconds		
Thermal Shock	MIL-STD-202, Method 107, Test Condition B, -55°C to +125°C, 30 minutes @ each extreme		
Mechanical Shock	MIL-STD-202, Method 213, Test Condition A - Half Sine, 50 G's, 11 msecs. duration		
High Frequency Vibration	MIL-STD-202, Method 204, Test Condition D		
Moisture Resistance	MIL-STD-202, Method 106, 50 cycles		
Terminal Strength	Board deflection per EIA / IS-722, 1mm deflection for 1 minute		
Terminal Attachment	MIL-STD-202, Method 211, Test Condition A, 5 lbs applied to end caps		

Part Numbering System



Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
24mm Tape and Reel	EIA RS-481-2 (IEC 60286-3)	2500	ER

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.

