477 Series, 5×20 mm, Time-Lag Fuse



Agency Approvals

Agency	Agency File Number	Ampere Range		
¢>	Cartridge: NBK040609-JP1021A NBK040609-JP1021C NBK100408-JP1021A Leaded: NBK040609-JP1021B NBK040609-JP1021D NBK040609-JP1021B	1A - 5A 6.3A - 12A 16A 1A - 5A 6.3A - 12A 16A		
(\mathbb{Z})	1620077	0.500A – 8A		
c FL us	E10480	0.500A - 16A		
VDE	40025413	1A, 3.15A		
A	J50248089	10A, 12A, 16A		
(€	N/A	0.500A – 16A		

Additional Information







Samples

Description

400Vdc/500Vac rated, 5x20mm, time-lag, surge withstand ceramic body cartridge fuse.

RoHS 🔞 🖘 c 🔁 us 🛇 🛆 🔬 🤆

Features

- Designed to International Available in cartridge and (IEC) Standard for use globally.
 - axial lead form • RoHS compliant and
- Follow the IEC 60127-2, Sheet 5 specification for time-lag fuses
 - lead-free

Applications

High energy and power efficient applications.

Electrical Characteristics for Series

% of Ampere Rating	Ampere Rating	OpeningTime		
150%	.58	60 minutes, Minimum		
	1 - 3.15	60 minutes, Minimum		
	4 - 6.3	60 minutes, Minimum		
	8 - 16	30 minutes, Minimum		
	.58	30 minutes, Maximum		
210%	1 - 3.15	30 minutes, Maximum		
210%	4 - 6.3	30 minutes, Maximum		
	8 - 16	30 minutes, Maximum		
	.58	.25 sec., Min.; 80 sec. Max.		
2750/	1 - 3.15	.75 sec., Min.; 80 sec. Max.		
275%	4 - 6.3	.75 sec., Min.; 80 sec. Max.		
	8 - 16	.75 sec., Min.; 80 sec. Max.		
	.58	.05 sec., Min.; 5 sec. Max.		
4000/	1 - 3.15	.095 sec., Min.; 5 sec. Max.		
400%	4 - 6.3	.15 sec., Min.; 5 sec. Max.		
	8 - 16	.15 sec., Min.; 5 sec. Max.		
	.58	.005 sec., Min.; .15 sec. Max.		
1000%	1 - 3.15	.01 sec., Min.; .15 sec. Max.		
1000%	4 - 6.3	.01 sec., Min.; .15 sec. Max.		
	8 - 16	.01 sec., Min.; .15 sec. Max.		



Axial Lead & Cartridge Fuses

5×20 mm > Time-Lag > 477 Series

Electrical Characteristic


		Max Voltage			Nominal Cold	Nominal	Agency Approvals				
	Amp Rating	Ratir	ıg (V)	Interrupting Rating	Resistance	Melting I²t (A² sec.)†	PS E	c Nus	(\mathbb{Z})	\triangle	
		AC	DC		(Milli-ohms)						
.500	0.5	500	400	100A@500VAC 1500A@400VDC	1055.900	0.300	-	X*	X**	-	-
.800	0.8	500	400		430.000	0.909	-	X*	x**	-	-
001.	1	500	400		139.400	1.800	x	X*	X**	-	X
002.	2	500	400		55.200	9.120	x	X*	x**	-	-
3.15	3.15	500	400		27.700	50.109	x	X*	X**	-	X
004.	4	500	400		17.200	52.480	x	X*	X**	-	-
005.	5	500	400		13.700	76.500	x	X*	X**	-	-
06.3	6.3	500	400	100A@500VAC	10.970	121.451	x	X	X**	-	-
008.	8	500	400	500A@400VDC	8.305	203.520	x	X	X**	-	-
010.	10	500	400		4.950	509.000	x	X	-	X	-
012.	12	500	400		4.730	576.000	x	X	-	X	-
016.	16	500	400	100A@500VAC 400A@400VDC	3.100	1331.200	x	x	-	x***	-

*100A @ 600Vac also available. Add suffix "MXE6P". Example: 0477004.MXE6P.


Semko approval for 100A@500Vac and 200A@400Vdc. *100A@ 500Vac and 300A@400Vdc for 16A

[†]I²t test at 10x rated current.

Temperature Re-rating Curve



Average Time Current Curves





Axial Lead & Cartridge Fuses

Recommended Process Parameters:

Note: These devices are not recommended for IR or Convection Reflow process

Wave Parameter

(Depends on Flux Activation Temperature)

Temperature Minimum:

Temperature Maximum:

Recommended Hand-Solder Parameters:

Preheat Time:

Solder Dwell Time:


Solder Pot Temperature:

Solder Iron Temperature: 350°C +/- 5°C Heating Time: 5 seconds max.

5×20 mm > Time-Lag > 477 Series

Preheat:

Soldering Parameters - Wave Soldering



Product Characteristics

Materials	Body: Ceramic Cap: Nickel-plated Brass Leads: Tin-plated Copper			
Terminal Strength	MIL-STD-202, Method 211, Test Condition A			
Solderability	MIL-STD-202 Method 208			
Product Marking	Cap 1: Brand logo, current and voltage ratings Cap 2: Series and agency approval markings			
Packaging	Available in Bulk (M=1000 pcs/pkg)			

20±0.5 -

21.5±1.0

21.5±1.0

Notes: * Ratings above 5A 1.0±0.05 diameter lead.

 5.1 ± 0.6

 5.1 ± 0.6

0477000XI

40±1.0

40+1 0

0 65+0 05*

↓ 5.2+0.1

0.2

5.5+0.3

All dimensions in mm

Operating Temperature -55°C to +125°C MIL-STD-202, Method 107, Test Condition B (5 Thermal Shock cycles, -65°C to +125°C) Vibration MIL-STD-202, Method 201 MIL-STD-202, Method 103, Test Condition A Humidity (High RH (95%) and elevated temp (40°C) for 240 hours) MIL-STD-202, Method 101, Test Condition B Salt Spray

0477 xxxx M X E P

Lead-Free Recommendation

(Typical Industry Recommendation)

100°C


150°C

60-180 seconds

260°C Maximum

2-5 seconds

Part Numbering System



Lead-Free

Packaging

Dimensions

0477.500XEF

to 0477.800XEP

0477001.XEP

0477016 XFP

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Reel Size			
477 Series							
Bulk	N/A	1000	MX	N/A			
Bulk	N/A	1000	MXE	N/A			
Reel and Tape	N/A	1000	MRET1	T1=53mm (2.087")			

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applicable to Littelfuse as set forth in applicable Littelfuse documentation. Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.