

NGRM-ENC SERIES

NGRM-ENC



Description

The NGRM-ENC Enclosed Neutral-Grounding-Resistor (NGR) Monitor series is a Type 4X enclosure housing a Littelfuse Startco SE-325 or SE-330 Neutral-Grounding-Resistor Monitor and optional accessories that include a 480/600-V control power transformer (CPT), faulted-phase indication (FPI); implemented with an EL3100 Ground-Fault & Phase-Voltage Indicator), earth-leakage panel meter, pulse-enable control, and mounting options. Appropriate fusing is included and field wiring is to terminal blocks.

Options



SE-325 Neutral-Grounding-Resistor Monitor

Measures current and voltage in a transformer or generator neutral-to-ground connection and continuity of the neutral-grounding resistor.



SE-330 Neutral-Grounding-Resistor Monitor

Advanced ground-fault and neutral-grounding resistor monitoring relay that measures neutral current, neutral-to-ground voltage, and neutral-to-ground resistance.



EL3100 Ground-Fault & Phase-Voltage Indicator

Three panel-mounted LEDs indicate the ground-faulted phase.



Panel Meter


Panel-mounted meter displays earth leakage current as a percentage of the ground-fault-CT-primary rating.



RK-332/RK-302 Remote Indication and Reset

Panel-mounted remote indication and reset assemblies are included with SE-325 and surface-mounted SE-330 configurations.

Simplified Circuit Diagram



NGR Assembly
(ordered separately)

NGRM-ENC
(SE-330 with voltage indication shown)

Ordering Information

The following options are available with a faster shipping time:

| ORDERING NUMBER | PROTECTION RELAY OPTION | NGR MONITOR MOUNTING OPTION | AMMETER & PULSE CONTROL OPTION | COMMS | CONTROL-POWER TRANSFORMER OPTION |
|-----------------|-------------------------|-----------------------------|--------------------------------|-----------------------|----------------------------------|
| NGRM-ENC-000-01 | SE-325 | Surface mounted | None | None | CPT |
| NGRM-ENC-200-01 | SE-330 (K4=NO) | Surface mounted | None | None | CPT |
| NGRM-ENC-201-01 | SE-330 (K4=NO) | Panel mounted | None | None | CPT |
| NGRM-ENC-201-11 | SE-330 (K4=NO) | Panel mounted | Ammeter | None | CPT |
| NGRM-ENC-230-01 | SE-330 (K4=NO) | Surface mounted | None | Ethernet/2 RJ45 ports | CPT |
| NGRM-ENC-231-01 | SE-330 (K4=NO) | Panel mounted | None | Ethernet/2 RJ45 ports | CPT |

NGRM-ENC SERIES

NGRM-ENC



Ordering Information

| | PROTECTION RELAY OPTION | NETWORK COMMUNICATIONS OPTION | NGR MONITOR MOUNTING OPTION | | AMMETER & PULSE CONTROL OPTION | CONTROL-POWER TRANSFORMER OPTION |
|-----------|--|--|--|---|--|--|
| NGRM-ENC- | X | X | X | – | X | X |
| | 0=SE-325 1=SE-325 & voltage indication ⁽¹⁾ 2=SE-330 (N.O. K4) 3=SE-330 (N.O. K4) & voltage indication ⁽¹⁾ 4=SE-330 (N.C. K4) 5=SE-330 (N.C. K4) & voltage indication ⁽¹⁾ 6=SE-330HV (N.O. K4) 7=SE-330HV (N.O. K4) & voltage indication ⁽¹⁾ 8=SE-330HV (N.C. K4) 9=SE-330HV (N.C. K4) & voltage indication ⁽¹⁾ | 0=No network communications 1=DeviceNet ⁽²⁾ 3=Ethernet, dual RJ45 ⁽²⁾ 4=Ethernet, 1 RJ45 & 1 fiber ⁽²⁾ 5=Ethernet, dual fiber ⁽²⁾ 6=IEC 61850, dual RJ45 ⁽²⁾ 7=IEC 61850, 1 RJ45 & 1 fiber ⁽²⁾ 8=IEC 61850, dual fiber ⁽²⁾ | 0=Surface-mounted NGR monitor ⁽⁴⁾ 1=Panel-mounted NGR monitor ⁽⁵⁾ | | 0=No ammeter 1=Earth-leakage panel meter ⁽²⁾ 2=Earth-leakage panel meter & pulse-enable switch ⁽³⁾ | 0=No CPT 1=480/600-V CPT ⁽¹⁾ |

Note (1) - Includes fuses, (2) - SE-330 models only, (3) - SE-330 models only, excluding SE-330HV models, (4) - Includes panel-mounted indication & reset, and USB connector for SE-330 models, (5) - SE-330 models only; includes IP65 hinged transparent cover

Specifications

| | |
|-------------------|---|
| Enclosure | Polyester, Lockable. SE-330 panel-mount options are rated to IP65. All other options are rated to Type 4X. |
| Dimensions | H 454 mm (17.9") W 406 mm (16") D 264 mm (10.4") Clearance required to open SE-IP65CVR-G 112 mm (4.4") |
| Approvals | cCSAus |
| Warranty | 1 year |