



DST560S-A

5A, 60V, TO-277B, Single

**Pinout****Description**

The DST Series is a Schottky Barrier Rectifier that provides ultra low forward voltage (V_F) and is designed to meet the general requirements of commercial and industrial applications by providing high temperature, low leakage and lower V_F .

It is suitable for high frequency switching mode power supply, free-wheeling diodes and polarity protection diodes.

Features

- High reliability application and AEC-Q101 qualified
- Ultra low forward voltage drop
- High frequency operation
- MSL: Level 1 - unlimited
- High junction temperature capability
- Trench MOS Schottky technology
- Single die in TO-277B Package
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/ JEDEC J-STD-609A.01)
- Halogen-free

Applications

- Switching mode power supply
- DC/DC converters
- Free-Wheeling diodes
- Polarity Protection Diodes

Maximum Ratings

Parameters	Symbol	Test Conditions	Max	Unit
Peak Inverse Voltage	V_{RWM}	—	60	V
Average Forward Current	$I_{F(AV)}$	50% duty cycle @ $T_L = 125^\circ\text{C}$ rectangular wave form	5	A
Peak One Cycle Non-Repetitive Surge Current	I_{FSM}	8.3 ms, half Sine pulse	100	A

Electrical Characteristics

Parameters	Symbol	Test Conditions	Typ	Max	Unit
Forward Voltage Drop*	V_{F1}	@2.5 A, Pulse, $T_J = 25^\circ\text{C}$	0.42	—	V
		@5 A, Pulse, $T_J = 25^\circ\text{C}$	0.50	0.70	
	V_{F2}	@2.5 A, Pulse, $T_J = 125^\circ\text{C}$	0.33	—	
		@5 A, Pulse, $T_J = 125^\circ\text{C}$	0.44	0.60	
Reverse Current*	I_{R1}	@ $V_R = \text{rated } V_R$, $T_J = 25^\circ\text{C}$	0.01	0.7	mA
	I_{R2}	@ $V_R = \text{rated } V_R$, $T_J = 125^\circ\text{C}$	6.4	25	
Junction Capacitance	C_T	@ $V_R = 5\text{ V}$, $T_C = 25^\circ\text{C}$, $f_{\text{SIG}} = 1\text{ MHz}$	314	—	pF

* Pulse Width < 300 μs , Duty Cycle < 2%

DST560S-A**5A, 60V, TO-277B, Single****Thermal-Mechanical Specifications**

Parameters	Symbol	Test Conditions	Max	Unit
Junction Temperature	T_J		-55 to +150	°C
Storage Temperature	T_{stg}		-55 to +150	°C
Maximum Thermal Resistance Junction to Ambient	R_{thJA}	DC operation	75	°C/W
Maximum Thermal Resistance Junction to Lead	R_{thJL}		4	°C/W
Approximate Weight	wt		0.08	g
Case Style	TO-277B			

Figure 1:
Typical Forward Characteristics




Figure 2:
Typical Reverse Characteristics






Figure 3:
Typical Junction Capacitance





DST560S-A

5A, 60V, TO-277B, Single

Dimensions-TO-277B


Symbol	Millimeters		
	Min	Typ	Max
A	6.30	6.50	6.70
B	5.28	5.38	5.48
C	3.88	3.98	4.08
D	2.90	3.05	3.20
E	3.40	3.55	3.70
F	4.20	4.40	4.60
G	1.70	1.80	1.90
I	1.74	1.84	1.94
J	0.65	0.85	1.05
K	0.85	0.90	0.95
L	0.95	1.10	1.25
M	0.20	0.25	0.30
N	0.25	0.40	0.55
O	4.00	4.05	4.25

Mounting Pad Layout**Part Numbering and Marking System**

DST	= Device Type
5	= Forward Current (5A)
60	= Reverse Voltage (60V)
S	= Package Type
A	= AEC-Q101 qualified device
LF	= Littelfuse
YY	= Year
WW	= Week
L	= Lot Number

Packing Options

Part Number	Marking	Packing Mode	M.O.Q
DST560S-A	DST560S-A	5000pcs / Reel	5000

Carrier Tape & Reel Specification

Symbol	Millimeters	
	Min	Max
A	4.28	4.48
B	6.80	7.00
d	1.40	1.60
d1	—	1.50
E	1.65	1.85
F	5.40	5.60
P	7.90	8.10
P0	3.90	4.10
W	11.70	12.30

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.

Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

