


SC1103C-01UTG

80A Discrete Bidirectional TVS Diode, Lightning Surge Protection

HF **RoHS** **Pb**


Description

The SC1103C includes TVS diodes fabricated in a proprietary silicon avalanche technology protect each I/O pin to provide a high level of protection for electronic equipment that may experience destructive electrostatic discharges (ESD). These robust diodes can safely absorb repetitive ESD strikes at $\pm 30\text{kV}$ (contact discharge, IEC 61000-4-2) without performance degradation. Additionally, each diode can safely dissipate 80A of 8/20 μs surge current (IEC 61000-4-5, 2nd edition) with very low clamping voltages.

Features

- ESD, IEC 61000-4-2, $\pm 30\text{kV}$ contact, $\pm 30\text{kV}$ air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Surge Tolerance, IEC 61000-4-5 2nd edition, 80A ($t_P=8/20\mu\text{s}$)
- Low clamping voltage
- Low leakage current
- Moisture Sensitivity Level(MSL -1)
- Halogen-Free, Lead-Free and RoHS-compliant

Pinout and Functional Block Diagram



Applications

- Switches / Buttons
- Test Equipment / Instrumentation
- Point-of-Sale Terminals
- Medical Equipment
- Notebooks / Desktops / Servers
- Computer Peripherals

Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

SC1103C-01UTG

80A Discrete Bidirectional TVS Diode, Lightning Surge Protection

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
P_{pk}	Peak Pulse Power ($t_p=8/20\mu s$)	720	W
T_{OP}	Operating Temperature	-40 to 125	°C
T_{STOR}	Storage Temperature	-55 to 150	°C

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Electrical Characteristics ($T_{OP}=25^\circ C$)


Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R \leq 1\mu A$	-	-	3.3	V
Breakdown Voltage	V_{BR}	$I_R = 1mA$	3.4	3.8	5	V
Leakage Current	I_{LEAK}	$V_R = 3.3V$	-	-	1	μA
Clamp Voltage ¹	V_C	$I_{pp}=40A, t_p=8/20\mu s, Fwd$	-	6	-	V
		$I_{pp}=80A, t_p=8/20\mu s, Fwd$	-	9	-	V
Dynamic Resistance ²	R_{DYN}	TLP; $t_p=100ns, I/O$ to GND	-	0.02	-	Ω
Peak Pulse Current	I_{pp}	$t_p=8/20\mu s$	-	-	80	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 30	-	-	kV
Diode Capacitance ¹	C_{IO-GND}	Reverse Bias=0V, $f=1MHz$	-	130	-	pF

Note:

1. Parameter is guaranteed by design and/or component characterization.

2. Transmission Line Pulse (TLP) with 100ns width, 0.2ns rise time, and average window $t_1=70ns$ to $t_2=90ns$

I-V Curve Characteristics



V_R Stand-off Voltage – Maximum voltage that can be applied to the TVS without operation







V_{BR} Breakdown Voltage – Maximum voltage that flows through the TVS at a specified test current (I_R)

V_C Clamping Voltage – Peak voltage measured across the TVS at a specified I_{ppm} (peak impulse current)

I_R Reverse Leakage Current – Current measured at V_R

SC1103C-01UTG


80A Discrete Bidirectional TVS Diode, Lightning Surge Protection

Capacitance vs Reverse Bias**Clamping Voltage vs I_{PP}** **Positive Transmission Line Pulsing (TLP) Plot****Negative Transmission Line Pulsing (TLP) Plot****IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage****IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage**

SC1103C-01UTG


80A Discrete Bidirectional TVS Diode, Lightning Surge Protection

8/20μs Pulse Waveform



Soldering Parameters


Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 120 sec
Average ramp up rate (Liquidus) Temp (T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		30 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		260°C




Ordering Information

Part Number	Package	Min. Order Qty.
SC1103C-01UTG	1.6x1.0mm DFN	3000

Part Marking System




Part Numbering System



SC1103C-01UTG


80A Discrete Bidirectional TVS Diode, Lightning Surge Protection

Package Dimensions — 1610DFN



Symbol	1.6x1.0mm DFN					
	Millimeters			Inches		
	Min	Typ	Max	Min	Typ	Max
A	0.45	0.50	0.55	0.018	0.020	0.022
A1	-	0.02	0.05	-	0.001	0.002
D	1.55	1.60	1.65	0.061	0.063	0.065
E	0.95	1.00	1.05	0.037	0.039	0.041
b	0.75	0.80	0.85	0.030	0.031	0.033
L	0.35	0.40	0.45	0.014	0.016	0.018
e	1.10 BSC			0.043 BSC		
h	0.15	0.20	0.25	0.006	0.008	0.010

Embossed Carrier Tape & Reel Specification — 1610DFN



Product Disclaimer: Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>.