

SP1007 Series

5pF 8kV Bidirectional Discrete TVS

HF **RoHS** **Pb**



Web Resources



Download ECAD models, order samples, and find technical resources at www.littelfuse.com


Pinout

SOD882



AEC-Q101 qualified

Functional Block Diagram



Description

The SP1007 diodes are fabricated in a proprietary back-to-back silicon avalanche technology. These diodes provide a high ESD (electrostatic discharge) protection level for electronic equipment. The SP1007 TVS can safely absorb repetitive ESD strikes at the maximum level specified in IEC 61000-4-2 international standard (Level 4, $\pm 8\text{kV}$ contact discharge) without performance degradation. The back-to-back configuration provides symmetrical ESD protection for data lines when AC signals are present.


Features and Benefits

- ESD, IEC 61000-4-2, $\pm 8\text{kV}$ contact, $\pm 15\text{kV}$ air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, IEC 61000-4-5, 2nd Edition 2A (8/20 μs)
- Low capacitance of 5pF (TYP @ $V_R=5\text{V}$)
- Low leakage current of 0.1 μA at 5V
- Space efficient 0402 footprint
- AEC-Q101 qualified for SOD882 package
- Moisture Sensitivity Level (MSL -1) for SOD882 package
- Halogen-free, lead-free and RoHS compliant

Applications

- Mobile Phones
- Smart Phones
- Camcorders
- Portable Medical
- Digital Cameras
- MP3/PMP
- Portable Navigation Components
- Tablets
- Point of Sale Terminals

Application Example



Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

SP1007 Series

5pF 8kV Bidirectional Discrete TVS

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
I_{PP}	Peak Current ($t_p=8/20\mu s$)	2.0	A
T_{OP}	Operating Temperature	-40 to 125	°C
T_{STOR}	Storage Temperature	-55 to 150	°C

Caution: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Electrical Characteristics ($T_{OP}=25^\circ C$)


Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R = 1\mu A$	-	-	6.0	V
Breakdown Voltage	V_{BR}	$I_R = 1mA$	-	8.5	9.5	V
Reverse Leakage Current	I_{LEAK}	$V_R = 5V$	-	0.1	0.5	μA
Dynamic Resistance ²	R_{DYN}	TLP, $t_p = 100ns$, I/O to GND	-	0.8	-	Ω
Clamp Voltage ¹	V_C	$I_{PP}=1A$, $t_p=8/20\mu s$, Fwd	-	10	50	V
		$I_{PP}=2A$, $t_p=8/20\mu s$, Fwd		12		
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 8	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 15	-	-	kV
Diode Capacitance ¹	$C_{I/O-I/O}$	Reverse Bias=0V $f=1MHz$	-	5	6	pF

Note:


1. Parameter is guaranteed by design and/or component characterization.

2. Transmission Line Pulse (TLP) with 100ns width, 2ns rise time, and average window $t_1=70ns$ to $t_2=90ns$

Capacitance vs. Reverse Bias




8/20 μs Pulse Waveform




SP1007 Series

5pF 8kV Bidirectional Discrete TVS

Insertion Loss (S21) I/O to GND



Transmission Line Pulsing(TLP) Plot




Product Characteristics of SOD-882 Package

Lead Plating	Pre-Plated Frame
Lead Material	Copper Alloy
Substrate material	Silicon
Body Material	Molded Compound
Flammability	UL Recognized compound meeting flammability rating V-0

Soldering Parameters


Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 120 secs
Average ramp up rate (Liquidus) Temp (T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		30 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		260°C



SP1007 Series

5pF 8kV Bidirectional Discrete TVS


Part Numbering System




Ordering Information

Part Number	Package	Min. Order Qty.
SP1007-01WTG	0201 Flipchip	10000
SP1007-01ETG	SOD882	10000

Part Marking System




SP1007-01WTG



SP1007-01ETG

Package Dimensions — SOD882




Symbol	Package	SOD882					
		JEDEC					
		MO-236					
		Millimeters			Inches		
		Min	Typ	Max	Min	Typ	Max
A		0.95	1.00	1.05	0.037	0.039	0.041
B		0.55	0.60	0.65	0.022	0.024	0.026
C		0.40	0.50	0.60	0.016	0.020	0.024
D			0.45			0.018	
E		0.20	0.25	0.30	0.008	0.010	0.012
F		0.45	0.50	0.55	0.018	0.020	0.022

SP1007 Series


5pF 8kV Bidirectional Discrete TVS

Embossed Carrier Tape & Reel Specification — SOD882



Symbol	Millimeters
A0	0.70+/-0.045
B0	1.10+/-0.045
K0	0.65+/-0.045
F	3.50+/-0.05
P1	2.00+/-0.10
W	8.00 + 0.30 -0.10

8mm TAPE AND REEL



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.