


344 Series Blown Fuse Indicating Holders for 3AG and 3AB Fuses


c**W**us



Dimensions



1.10"



.<u>567"</u> .575"

Product Characteristics

Compatible Fuses	3AG, <u>3AB</u>				
Electrical	Rated at 20 amperes at lamp voltage shown below. Dielectric: withstanding voltage exceeds 1500 volts. All fuseholders are supplied with a resistor. When designing indicating type fuseholders into a circuit, consideration should be given to the resistance of fractional amperage fuses and the parallel resistance of the indicator lamp and its resistor				
Mounting	Withstands 15 lbin. mounting torque. Maximum panel thickness is .250"				
Molded Parts	Black Body and knob are thermoset (UL94 V-0), except lens is thermoplastic (UL 94HB). See Table below for lens color				
Knob	Bayonet style				
Terminals	Copper & copper alloy. Tin plated				
Ambient Temperature	-40 ℃ to +85 ℃				
Hardware	Neoprene washer, lockwasher & hex nut unassembled. O-ring option available must be ordered separately using part number 901-108 formation or group function of a state				

Refer to **Fuseology** for information on proper fuseholder re-rating

Agency Approvals

Agency	Agency File Number			
91	E14721			

Ordering Information								
Catalog Number								
344 000 Series (Bar Knob)	344 400 Series (Round Knob)	Voltage Range	Lamp Type Rating	Lamp Current Rear Panel	Lens Color			
344 006	344 401	2.5 to 7	6V Incandescent	.20 amp	Amber			
344 012	344 402	7 to 16	14V Incandescent	.08 amp	Amber			
344 024	344 403	16 to 32	28V Incandescent	.04 amp	Amber			
344 125	344 404	100 to 125	Neon	.002 amp	Clear			
344 250	344 405	200 to 250	Neon	.002 amp	Clear			

Additional Information





2.67" MAXIMUM WITH FUSE INSTALLED



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.