





LTR	DATE	REVISION	CHK	APD
A	1/6/00	60176 - RELEASED	JMB	



SECTION A-A

- NOTES: UNLESS OTHERWISE SPECIFIED
1. MAXIMUM FLASH LIMITS: .005" HEIGHT, .007" WIDTH.
 2. ALL DIMENSIONS ARE TYPICAL FOR REPEATED FEATURES.
 3. ○ ENDS MUST BE CAPABLE OF BEING SQUEEZED TO BOTTOM AND RETURN TO ITS NORMAL POSITION.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
----	--------------	-------------	-------	-----

BILL OF MATERIAL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
○	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE			
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			
COPIES TO		MATL SPEC		
1	9	18	NYLON 6/6	
2	10	19	FINISH	
3	12	20		
4	13	21	DRW	JMB DATE 1/6/00 SCALE 4:1
5	14	23	CHK	JMB DATE 1/6/00 SUPER DR
6	15	33	CHK	JMB DATE 1/6/00 SUPER DR
7	16	43	APP	JMB DATE 1/6/00 SUPER DR
8	17	53	APP	JMB DATE 1/6/00 SUPER DR
UNLESS OTHERWISE SPECIFIED		FRACTION ±		
TOLERANCE UNITS		ANGULAR ±1°		
THREE PLACE DEC		THREE PLACE DEC		

TITLE	REVISION	DRWG. NO.	OUTLINE
FUSE INSERTER AND EXTRACTOR (STD. & MINI ATO FUSES)	A	00970038Z	