




NOTES:

1. MAX. RATING (SEE CHART), 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	FINISH	
1	9 18	DRW PJM	DATE 9/4/01	SCALE 1:1
2	10 19			
3	12 20	CHK	DATE	SUPER DRW
4	13 21			
5	14 23	APPD	DATE	RAW STK WT
6	15 33			LB/M
7	16 43	TOLERANCE UNLESS OTHERWISE SPECIFIED		
8	17 53	TWO PLACE DEC $\pm$.01 FRACTION $\pm$		
		THREE PLACE DEC $\pm$.005 ANGULAR $\pm$ 1°		
TITLE		MINIFUSE HOLDER, IN LINE		
LTR		REVISION		CHK
A	60655 - RELEASE 9/4/01 PJM			APD
				DRAWG. NO. SERIES OUTLINE
				01530028Z
		DES PLAINES, ILLINOIS 60016		A

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

9 DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST-100 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN ATTENDANCE INSPECTION INSTRUCTIONS.

CP VALUE
MUST BE WITHIN THE DIMENSIONAL LIMITATIONS
SHOWN ON DRAWING AND INITIALLY LOCATED TO
ALLOW FOR MAXIMUM TOOL LIFE.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS	DENOTES CRITICAL CHARACTERISTIC
CPK	DENOTES CPK DIMENSIONS - MINIMUM
ST	DENOTES A CHARACTERISTIC THAT AFFECTS PROCESS PERFORMANCE, PROCESS CONTROL AND TRACKING TO BE DEFINED IN THE UTILITY USE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS - MINIMUM
	MUST BE WITHIN THE DIMENSIONS SPECIFIED ON DRAWING AND INITIALLY APPROVED FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT