



NOTES:

- RESISTOR: 121 OHMS ±1%, 1/2 WATT (METAL FILM).
- 0.51 [.020] MAX. MOLD SINKS ARE PERMISSIBLE.

METRIC

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD
A	06/07/15	514526GCA-RELEASE	OPL	

  

COPIES TO	MATL SPEC	FINISH	SCALE	GRAMS/PIECE
1 9 18			4:1	
2 10 19			SUPER DR	
3 12 20				
4 13 21	DRW OPL		DATE 06/07/15	
5 14 23			DATE	
6 15 33			DATE	
7 16 43			FINISH GOOD WT	
8 17 53				

  

TOLERANCE UNLESS OTHERWISE SPECIFIED	
ONE PLACE DEC	+/- .3
TWO PLACE DEC	+/- .25
THREE PLACE DEC	+/- .100
ANGULAR	+/- 1°

  

3RD ANGLE PROJECTION	

  

TITLE	RESISTOR ASSEMBLY
 DES. PLAINES, ILLINOIS 60016	REVISION DRWG. NO. A OL-02400107P-DE OUTLINE