







- NOTES:
- 1) BASE: UL94V-0 GLASS-FILLED PPA
  - M8 STUDS: SEE CHART
  - COVER: UL94V-0 ELASTOMER
  - 2) MAX FUSE RATING: 500A
  - 3) M8 STUD TORQUE: 12-18Nm
  - MOUNTING TORQUE (W/M6 BOLTS & WASHERS): 5Nm
  - 4) TEMPERATURE RATING: -40°C TO 125°C
  - 5) WIRE SIZE: 8mm<sup>2</sup> TO 30mm<sup>2</sup>



METRIC

| NO                                                                                               |                                                                                                                                                                         | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
|--------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|-------------|-------|-----|
| BILL OF MATERIAL                                                                                 |                                                                                                                                                                         |              |             |       |     |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES |                                                                                                                                                                         |              |             |       |     |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.                                   |                                                                                                                                                                         |              |             |       |     |
| ⊙                                                                                                | DENOTES CRITICAL CHARACTERISTICS.                                                                                                                                       |              |             |       |     |
| CPK                                                                                              | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE                                                                                                                              |              |             |       |     |
| ST                                                                                               | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS |              |             |       |     |
| CP                                                                                               | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE               |              |             |       |     |

| COPIES TO            |    | MATL SPEC                       |                                                          | SEE NOTES |                                  |
|----------------------|----|---------------------------------|----------------------------------------------------------|-----------|----------------------------------|
| 1                    | 9  | 18                              | TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK) | FINISH    | N/A                              |
| 2                    | 10 | 19                              |                                                          | DRW       | OPL                              |
| 3                    | 12 | 20                              |                                                          | CHK       | DATE                             |
| 4                    | 13 | 21                              |                                                          | DATE      | SCALE                            |
| 5                    | 14 | 23                              |                                                          | DATE      | SUPER DR                         |
| 6                    | 15 | 33                              |                                                          | DATE      | FINISH GOOD WT                   |
| 7                    | 16 | 43                              |                                                          | DATE      | GRAMS/PIECE                      |
| 8                    | 17 | 53                              |                                                          | DATE      | UP TO OVER UP TO OVER UP TO OVER |
| DIMENSION            |    | 0.5 - 3                         | 3 - 6                                                    | 6 - 30    | 30 - 120                         |
| TOLERANCE            |    | +0.1                            | +0.1                                                     | +0.2      | +0.3                             |
| 3RD ANGLE PROJECTION |    | TITLE                           |                                                          |           |                                  |
|                      |    | FLEX-MEGA ASSY WITHOUT HARDWARE |                                                          |           |                                  |
|                      |    | REVISION DRWG. NO.              |                                                          |           |                                  |
|                      |    | A OL-02981028HXFC-NH            |                                                          |           |                                  |