
Cartridge Fuse Blocks

Fuse Block > 656 Series

656 Series Molded Base PC Mount Fuse Block For 5×20mm Fuses





Agency Approval

Agency	Agency File Number
© ^V E	40001499
c FL °us	E70164

Additional Information












Samples


Product Characteristics

Compatible Fuse Size	<u>5×20mm</u>
Materials	Holder: Black Thermoplastic UL94 V-0
iviateriais	Metal Parts: Tin plated copper alloy
Electrical Data	Rated Voltage: VDE 250 VAC UL 500 VAC/DC
	Rated Current: 16 A (UL)/10 A (VDE)
	Rated Power Acceptance (at ambient air temp 23 °C): - 4 W without cover - 4 W with 660 cover - 2.5 W with 659 cover
Mounting	656: Solder pins 0.4mm×1.1mm Ø 2.7mm screw hole may be used optionally
Operating Temperature	-40 °C to +85 °C
Climatic Category	40/085/21 according to IEC 60068-1
Stock Conditions	0 °C to 60 °C, at max. 70% relative humidity
Vibration Resistance	According to IEC 60068-2-6, Test Fc
Contact Resistance	<5 mΩ
Dielectric Strength	> 3 kV, 50 Hz, 1 min.
Impulse withstand Voltage	> 4 kV between life parts
Insulation Resistance	(500 V DC/1 min): >10 $M\Omega$ between live parts of different potentials
Solderability	245 °C/3 sec. according to IEC 60068-2-20, Test Ta, method 1
Soldering Heat Resistance	260 °C/10 sec. according to IEC 60068-2-20, test Tb method 1
Minimum Cross Section	Conducting path - 0.2 mm ²
Torque/fixing screw	Max. 0.3 Nm

Note: If used with covers, refer to Fuseology for information on proper fuse block re-rating.


Dimensions






Max. dimension for removal of cover Dimensions in Millimeters

Re-rating Curves





Cartridge Fuse Blocks


Fuse Block > 656 Series

Soldering Parameters-Wave Soldering

Wave Parameter	Lead-Free Recommendation	
Preheat: (Depends on Flex Activation Temperature)	(Typical Industry Recommendation)	
Temperature Minimum	100 °C	
Temperature Maximum	150 °C	
PreheatTime	60-180 seconds	
Solder Pot Temperature	260 °C Maximum	
Solder Dwell Time	2-5 seconds	

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350 $^{\circ}\text{C}$ +/- 5 $^{\circ}\text{C}$ Heating Time: 5 seconds max.



Ordering Information

Part Number	Description	Packaging
65600001009	Fuse Block - "A" dimension 22.5mm	Bulk Pack (100 Pcs)
65600001409	Fuse Block - "A" dimension 25mm	Bulk Pack (100 Pcs)
6590000009	Fuse Holder Cover - Transparent plastic	Bulk Pack (100 Pcs)
6600001009	Fuse Holder Cover - Opaque plastic, suitable for infrared (IR) reflow soldering process	Bulk Pack (100 Pcs)

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.