Gas Discharge Tubes SE Series



RoHS

(P) 54


SE Series



Agency Approvals

AGENCY	AGENCY FILE NUMBER	
91	E128662	

2 Electrode GDT Graphical Symbol



Additional Information







Description

Littelfuse SE series GDT offers high surge ratings in a miniature package. It's designed for surface mounting on PCB with small size 3.2x1.6x1.6mm. Low insertion loss is perfectly suited to broadband equipment applications. The capacitance does not vary with voltage, and will not cause operational problems with ADSL2+, where capacitance variation across Tip and Ring is undesirable. These devices are extremely robust and are able to divert a 500A-600A pulse in a miniature package 1206 without destruction.

Features

- RoHS compliant and Lead-free
- GHz working frequency
- Excellent stability on
- multiple pulse duty cycleExcellent response to fast rising transients.
- Ultra Low Insertion Loss
- 0.5-0.6KA surge capability tested with 8/20µS pulse as defined by IEC 61000-4-5
- Ultra small devices offered in a variety of mounting lead forms
- Non-Radioactive
- Low capacitance (<0.5pF)
- Voltage Ranges 140V to 500V
- UL recognized
- Conforms to ITU-T K12, IEC 1000-4-5
- Square Outline

Applications

- Communication equipment
- CATV equipment
- Test equipment
- Data lines
- Power supplies
- Telecom SLIC protection

- Broadband equipment
- ADSL equipment, including ADSL2+
- XDSL equipment
- Satellite and CATV equipment
- General telecom
 equipment




Electrical Characteristics

	Device Specifications (at 25°C)							Life Ratings				
Part	DC Breakdown in Volts (@100V/s)		S	Impulse Breakdown in Volts (@100V/µs)	Impulse Breakdown In Volts (@1 Kv/µsec)	Insulation Resistance	Capacitance (@1MHz)	Arc Voltage (@1A)	Glow to Arc Transition Current	Glow Voltage	Discharge Current	Current
Number	MIN	TYP	MAX	MAX		MIN	MAX				(x 10 @8/20µs)	(x10 @5/320µs)
SE140	98	140	182	800	900		<0.5 pf		<1.0 A			
SE200	140	200	260	700	1100		<0.3 pf		<1.0 A		0.5 kA	
SE230	172	230	276	600	800	>1GΩ (at 100VDC)	<0.5 pf	~10 V	<1.0 A	~60 V	0.5 KA	150 A
SE350	265	350	495	900	1150		<0.5 pf	~10 V	<1.0 A	~60 V		150 A
SE470	329	470	611	1050	1200		<0.3 pf		<1.0 A		0.5 kA	
SE500	400	500	600	1050	1200		<0.3 pf		<1.0 A		0.5 kA	


Product Characteristics

Materials	Device Tin Plated 17.5±12.5 Microns Construction Ceramic Insulator.	
Storage and Operational Temperature	-40 to +90 °C	


Voltage vs. Time Characteristic



Tape and Reel Dimensions (IEC 60286-3, dimension in mm)




Reel Specifications IEC 60286-3 Dimensions in mm







Soldering Parameters - Reflow Soldering (Surface Mount Devices)

Reflow Co	ndition	Pb – Free assembly	
	-Temperature Min (T _{s(min)})	150°C	
Pre Heat	-Temperature Max (T _{s(max)})	200°C	
	-Time (Min to Max) (t _s)	60 – 180 secs	
Average ra (T _L) to pea	amp up rate (LiquidusTemp k	3°C/second max	
$T_{S(max)}$ to T_{L}	- Ramp-up Rate	5°C/second max	
Reflow	-Temperature (T_L) (Liquidus)	217°C	
	-Temperature (t _L)	60 – 150 seconds	
PeakTemp	erature (T _P)	260 ^{+0/-5} °C	
Time with Temperatu	in 5°C of actual peak ıre (t _p)	10 – 30 seconds	
Ramp-dov	vn Rate	6°C/second max	
Time 25°C	to peakTemperature (T _P)	8 minutes Max.	
Do not exc	ceed	260°C	



Device Dimensions





Recommended Pad Layout

Part Numbering System and Ordering Information

SE xx	X
Series ————————————————————————————————————	
Breakdown Voltage –	J
140 = 140V	
200 = 200V	
230 = 230V	
350 = 350V	
470 = 470V	
500 = 500V	

Packaging

Part Number	Packaging Option	Quantity
SE140	Tape and Reel	3,000
SE200	Tape and Reel	3,000
SE230	Tape and Reel	3,000
SE350	Tape and Reel	3,000
SE470	Tape and Reel	3,000
SE500	Tape and Reel	3,000

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.

© 2017 Littelfuse, Inc. Specifications are subject to change without notice. Revised: 12/12/17