



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
- VOLTAGE RATING: 32VDC
- TEMP. RATING: -40°C - 125°C
- CABLE TYPE: XLPE, SAE J1128, TXL (10 AWG)
- SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
- BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

COMPONENT NO		DESCRIPTION	QTY/M	U/M
<b>BILL OF MATERIAL</b>				
COPIES TO	MATL SPEC	FINISH		
1 9	18	DATE	SCALE	FULL
2 10	19	PJM	02/25/02	
3 12	20	CHK	DATE	SUPER DRW
4 13	21	APPD	DATE	FINISH GOOD WT
5 14	22			GRAMS/PIECE
6 15	23			
7 16	43	TOLERANCE UNLESS OTHERWISE SPECIFIED		
8 17	53	TWO PLACE DEC ±.25[.01] FRACTION ±		
		THREE PLACE DEC ±.100[.004] ANGULAR ±1°		
3RD ANGLE PROJECTION		TITLE		
		CABLEPRO		
		DRWG. NO.	OUTLINE	
		E	0496060.7XA	

LTR	REVISION	CHK	APD
A	60790 - RELEASED 02/25/02 PJM		
B	82373B-CHG 50 TO 65 & 350 TO 365.8 7/31/02 PJM		
C	82514B-CHG 240±5[9.449] TO 230±5[9.055] & 365.8±10 [14.402] TO 355.8±10 [14.008] 10/07/02 PJM		
D	83705B- ADDED BAR CODE 5/21/04 JMB		
E	84765B-ADD NOTES FOR BAR CODE 05/31/06 DHM		

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.  
DIMENSIONS IN BRACKETS [ ] ARE INCHES  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.  
DENOTES CRITICAL CHARACTERISTICS.  
DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE  
DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION  
OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT  
SHOULD BE USED AS INDICATED IN THE INSTRUCTIONS.  
CP DIMENSIONS, -MINIMUM CP VALUE  
DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS  
SHOULD BE WITHIN THE DIMENSIONAL LIMITATIONS  
AND LOCATED AS SHOWN IN THE DRAWING AND INITIALLY LOCATED TO  
AND FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

