



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

INTERRUPT RATING: 2000A @ 32VDC

VOLTAGE RATING: 32VDC

TEMP. RATING: -40°C - 125°C

CABLE TYPE: XLPE, SAE J1127, STX (4AWG)

SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION

APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.

BAR CODE OR
DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY.
IT IS LOCATED ON ONE OF THE CABLE LEADS.

LITTLEFUSE INSPECTION INSTRUCTIONS. DATE CP DIMENSIONS, -MINIMUM CP VALUE DATE WITHIN THE DIMENSIONAL LIMITATIONS DATE DRAWING AND/OR INITIALS LOCATED TO DATE FOR MAXIMUM TOOL LIFE..														NO		COMPONENT NO		DESCRIPTION		QTY/M		U/M																																												
BILL OF MATERIAL																																																																		
COPIES TO <table><tr><td>1</td><td>9</td><td>18</td></tr><tr><td>2</td><td>10</td><td>19</td></tr><tr><td>3</td><td>12</td><td>20</td></tr><tr><td>4</td><td>13</td><td>21</td></tr><tr><td>5</td><td>14</td><td>23</td></tr><tr><td>6</td><td>15</td><td>33</td></tr><tr><td>7</td><td>16</td><td>43</td></tr><tr><td>8</td><td>17</td><td>53</td></tr><tr><td colspan="3">3RD ANGLE PROJECTION</td></tr></table> MATL SPEC <table><tr><td>DRW</td><td>PJM</td><td>DATE</td><td>12/03/03</td><td>SCALE</td><td>FULL</td></tr><tr><td>CHK</td><td></td><td>DATE</td><td></td><td>SUPER DRW</td><td></td></tr><tr><td>APPD</td><td></td><td>DATE</td><td></td><td>FINISH GOOD WT</td><td>GRAMS/PIECE</td></tr></table>														1	9	18	2	10	19	3	12	20	4	13	21	5	14	23	6	15	33	7	16	43	8	17	53	3RD ANGLE PROJECTION			DRW	PJM	DATE	12/03/03	SCALE	FULL	CHK		DATE		SUPER DRW		APPD		DATE		FINISH GOOD WT	GRAMS/PIECE	TITLE CABLEPRO		REVISION C		DWG. NO. 0496200.ZXF		OUTLINE 0496200.ZXF	
														1	9	18																																																		
														2	10	19																																																		
														3	12	20																																																		
														4	13	21																																																		
5	14	23																																																																
6	15	33																																																																
7	16	43																																																																
8	17	53																																																																
3RD ANGLE PROJECTION																																																																		
DRW	PJM	DATE	12/03/03	SCALE	FULL																																																													
CHK		DATE		SUPER DRW																																																														
APPD		DATE		FINISH GOOD WT	GRAMS/PIECE																																																													
LTR														REVISION				CHK		APD																																														
A														61316 - RELEASED 12/03/03 PJM																																																				
B														83705B- ADDED BAR CODE 5/21/04 JMB																																																				
C														84765B-ADD NOTES FOR BAR CODE 05/31/06 DHM																																																				

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.

ALL DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED; DIMENSIONS DO NOT INCLUDE PLATING.

Q DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

7 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION

STANDARD TRACKING TO BE DEFINED IN
PROCEDURE OF PROCESS PERFORMANCE.

SELF INSPECTION INSTRUCTIONS.

CP DIMENSIONS, -MINIMUM CP VALUE
BE WITHIN THE DIMENSIONAL LIMITATIONS

ON DRAWING AND INITIAL
FOR MAXIMUM TOOL LIFE.

10

2

cul

10

ER

100

2015

LE

IN

FF

[illegible]
