



PART NUMBER	COVER OPENINGS
04980913ZXT	A D



LETTER DESIGNATIONS REFER TO POSITIONS OF AVAILABLE COVER OPENINGS. (SEE CHART)



NOTES:

- TAB OF COVER TIE IS INSERTED INTO HOLE IN BASE.
- TORQUE REQUIRED FOR TOP NUT (NOT SHOWN) TO BE 4.0 - 5.0 NEWTON METERS (35-44 IN-LBS).
- CAP SCREW AND JAM NUT - M5 X 0.8 STEEL, ZINC PLATE WITH TRIVALENT CHROMATE, LEACHED AND SEALED, INTEGRAL TORQUE CONTROL LUBRICANT FINISH. (MEETS 96 HR. ASTM STD. B-117 SALT SPRAY REQ.).
- HOLDER MEETS L/F VALIDATION TEST SPEC. VS-005004.

METRIC

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATERIAL SPEC			
1	9	18	FINISH		
2	10	19			
3	12	20			
4	13	21	DRW	DJG	SCALE 1:1
5	14	23	CHK		SUPER DR
6	15	33	APPD		DATE
7	16	43			FINISH GOOD WT
8	17	53			GRAMS/PIECE
TOLERANCE UNLESS OTHERWISE SPECIFIED					
ONE PLACE DEC +/- .25					
TWO PLACE DEC +/- .13					
THREE PLACE DEC +/- .100					
ANGULAR +/- 1°					
3RD ANGLE PROJECTION		TITLE			
		MIDI FUSE HOLDER			
		WITH WIDE OPENINGS			
		REVISION			
		B			
		DRWG. NO.			
		04980913ZXT			
		OUTLINE			