




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.


REVISIONS				
REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	First issue of outline drawing	17-Nov-20	L.Dal Molin	M.Tinto




12		Label		1	EA
11		M10 nut	Steel	2	EA
10		Spring washer	Steel	2	EA
9		Plane washer	Steel	2	EA
8		Screws M10	Copper	2	EA
7		Contacts-holder cover	Thermosetting	1	EA
6		Label		1	EA
5		Housing	Thermoplastic	1	EA
4		Cable clamp	Thermoplastic	1	EA
3		3-ways wiring		1	EA
2		Gasket	Rubber	1	EA
1		4-ways cap housing connector	Thermoplastic	1	EA
POS.	P/N	DESCRIPTION	MATERIAL	Q.TY	U/M




FORBIDDEN ORIENTATIONS



MOUTING TEMPLATE



SCHEMA ELETTRICO Elettrical diagram



FEATURES

- Voltage range: 10.5÷16V
- Max continuos current: 250A
- Max short term current: 800A per 30"
- Other features in accordance with Littelfuse Data Sheet
- Test in accordance with Littelfuse Test Specification

NOTES:

- Supplying state: main-contact open
- Nuts and bolts are supplied by separate packing
- Locking torque M10 nuts in equipment 18±1 Nm
- Fix the device to the chassis by means of M8 screws to be locked at 10±2 Nm

SAP drawing number:

Material and treatments:

REVISIONS

REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	First issue of outline drawing	17-Nov-20	L.Dal Molin	M.Tinto

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.

linear dimensions						
0,5	>3	>6	>30	>120	>400	>1000
3	6	30	120	400	1000	2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3

angle (for range of lengths)			
up to 10	>10 50	>50 120	>120 400
±1°30'	±1°	±0°30'	±0°15'

●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMEND AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NAME	DATE	 Expertise Applied Answers Delivered	
DRAWN	L.Dal Molin		
CHECKED	-		
	-		
	-		
FORM NO:	CVP-PE40-0013 REV A	TITLE	
FIRST ANGLE PROJECTION		General Electrical Main Switch	
		TGC/RME-C1 12V (+)	
		SIZE: A3	OUTLINE REV. A
DO NOT SCALE DRAWING	SCALE 1:2	OL-08070400	
		SHEET 1 OF 1	