



RIVETS (4X)

WHITE HOT STAMP ONE SIDE

BAR CODE OR DATE CODE (SEE NOTES)

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:
 INTERRUPT RATING: 2000A @ 32VDC
 VOLTAGE RATING: 32VDC
 TEMP. RATING: -40°C - 125°C
 CABLE TYPE: XLPE, SAE J1127, STX (4AWG), COLOR RED.
 SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
 APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
 BAR CODE OR DATA CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

METRIC
ASSEMBLY

◀S▶	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE.
●	CRITICAL CHARACTERISTIC FOR PART FIT/FUNCTION.
CPK	CPK DIMENSION. 1.67 MINIMUM CPK VALUE ON NEW TOOLING.
ST	STATISTICAL PROCESS CONTROL DIMENSION. THIS DIMENSION INDICATES PROCESS PERFORMANCE. DATA SHALL BE TRACKED AND ANALYZED AT PERIODIC TIMES, ACC. TO CONTROL PLAN.
CP	CP DIMENSION. 1.67 MINIMUM CP VALUE. MUST BE INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.
Ⓞ	CUSTOMER-DESIGNATED CHARACTERISTIC. REQUIREMENT FOR EACH SYMBOL TO BE DEFINED IN A CONVERSION TABLE.
Ⓐ	CLAMP DIMENSION. PARTS SHALL BE SECURED BEFORE TAKING DIMENSIONAL MEASUREMENTS. FIXTURING DATUMS & PROCEDURES TO BE DEFINED IN NOTES OR SEPARATE PROCESS DOCUMENTS.

DIMENSIONS & TOLERANCES ACC. TO ASME Y14.5-2009	MATERIAL SPEC	FINISH	DRW	CHK	DATE	REVISION		DRW
						SCALE	TITLE	
3RD ANGLE PROJECTION			JJR		04/15/05			
TOLERANCES UNLESS OTHERWISE SPECIFIED								
LINEAR DIMENSIONS			ANGLES			RADI		
DIM	UP TO .5	6 - 30	UP TO 30	120 - 400	UP TO 120	±0.5°	±0.2	
TOL	±0.1	±0.2	±0.3	±0.5				
CABLEPRO								
LITTELFUSE							REVISION	DRWG. NO.
CHICAGO, USA 773-628-1000							C	OL-0496200.ZXX
OUTLINE								