



NOTES:  
 INTERRUPT RATING: 2000A @ 32VDC  
 VOLTAGE RATING: 32VDC  
 TEMP. RATING: -40°C - 125°C  
 CABLE TYPE: XLPE, SAE J1127, STX (4AWG), COLOR RED.  
 SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION  
 APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.  
 BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

**METRIC**  
ASSEMBLY

◀S▶	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE.
●	CRITICAL CHARACTERISTIC FOR PART FIT/FUNCTION.
CPK	CPK DIMENSION. 1.67 MINIMUM CPK VALUE ON NEW TOOLING.
ST	STATISTICAL PROCESS CONTROL DIMENSION. THIS DIMENSION INDICATES PROCESS PERFORMANCE. DATA SHALL BE TRACKED AND ANALYZED AT PERIODIC TIMES, ACC. TO CONTROL PLAN.
CP	CP DIMENSION. 1.67 MINIMUM CP VALUE. MUST BE INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.
Ⓞ	CUSTOMER-DESIGNATED CHARACTERISTIC. REQUIREMENT FOR EACH SYMBOL TO BE DEFINED IN A CONVERSION TABLE.
Ⓐ	CLAMP DIMENSION. PARTS SHALL BE SECURED BEFORE TAKING DIMENSIONAL MEASUREMENTS. FIXTURING DATUMS & PROCEDURES TO BE DEFINED IN NOTES OR SEPARATE PROCESS DOCUMENTS.

DIMENSIONS & TOLERANCES ACC. TO ASME Y14.5-2009	MATERIAL SPEC	FINISH	DRW	PJM	CHK	DATE	06/08/04	SIZE	<b>B</b>	
										SCALE
3RD ANGLE PROJECTION	TOLERANCES UNLESS OTHERWISE SPECIFIED									
LINEAR DIMENSIONS	UP TO .5	6	UP TO 30	30 - 120	120 - 400	UP TO 400	ANGLES	±0.5°	RADII	±0.2
TOL	±0.1	±0.2	±0.3	±0.5	±0.5	±0.5	TITLE			
CABLEPRO										
LITTELFUSE®										
CHICAGO, USA 773-628-1000										
REVISION DRWG. NO. C 0L-0496200.ZXT										
OUTLINE										

LTR	DATE	REVISION	DRW
A	06/08/04	61470 - RELEASED	PJM
B	05/31/06	84765B-ADD NOTES FOR BAR CODE	DHM
C	22/APR/19	520732ECA-UPDATE TOLERANCE & DRAWING FORMAT	OPL