


NOTES:
INTERRUPT RATING: 2000A @ 32VDC
VOLTAGE RATING: 32VDC
TEMP. RATING: -40°C - 125°C
CABLE TYPE: XLPE SAE J1127, STX (4AWG) 125°C COLOR RED.
SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
BAR CODE OR
DATA CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY.
IT IS LOCATED ON ONE OF THE CABLE LEADS.

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DUAL DIMENSIONS IN BRACKETS [] ARE INCHES AND FOR REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.									
◀▶	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE.								
●	CRITICAL CHARACTERISTIC FOR PART FIT/FUNCTION.								
CPK	CPK DIMENSION. 1.67 MINIMUM CPK VALUE ON NEW TOOLING.								
ST	STATISTICAL PROCESS CONTROL DIMENSION. THIS DIMENSION INDICATES PROCESS PERFORMANCE. DATA SHALL BE TRACKED AND ANALYZED AT PERIODIC TIMES, ACC. TO CONTROL PLAN.								
CP	CP DIMENSION. 1.67 MINIMUM CP VALUE. MUST BE INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.								
Q	CUSTOMER-DESIGNATED CHARACTERISTIC. REQUIREMENT FOR EACH SYMBOL TO BE DEFINED IN A CONVERSION TABLE.								
△	CLAMP DIMENSION. PARTS SHALL BE SECURED BEFORE TAKING DIMENSIONAL MEASUREMENTS. FIXTURING DATUMS & PROCEDURES TO BE DEFINED IN NOTES OR SEPARATE PROCESS DOCUMENTS.								

DIMENSIONS & TOLERANCES ACC. TO ASME Y14.5-2009		MATL SPEC		-		SIZE			
3RD ANGLE PROJECTION 		FINISH		-					
SCALE 1:1		DRW	OPL	CHK	ER	DATE 27MAY19			
TOLERANCES UNLESS OTHERWISE SPECIFIED									
LINEAR DIMENSIONS									
DIM	UP TO .5 - 6	OVER 6 - 30	UP TO 30 - 120	OVER 120 - 400	UP TO		ANGLES		RADII
TOL	±0.1	±0.2	±0.3	±0.5			±0.5°		±0.2
TITLE									
CABLEPRO 32V 200A									
LTR		DATE		REVISION				DRW	
A		27MAY19		520766GCA-RELEASE				OPL	