



REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial Release	18-Jul-22		L.Dal Molin	M.Tinto



- PREScriptions
- Torque of screw M10=19 Nm max
 - Fix the device with M6 screw and with torque of 6±2 Nm

- CHARACTERISTICS
- Nominal working tension: 12-24V
 - Nominal working current main contact: 250A
 - Nominal max current main contact: 2000A for 5sec.
 - Number of mechanical operations: 150.000
 - Number of electrical operations: 50.000

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10 50	>50 120	>120 400			
±1°30'	±1°	±0°30'	±0°15'			
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
NAME		DATE		 Expertise Applied Answers Delivered		
DRAWN		L. Dal Molin 18-Jul-22				
CHECKED		-				
		-				
FORM NO: CVP-PE40-0013 REV A		TITLE				
FIRST ANGLE PROJECTION		TGC/MGE-MS7 +/- 12-24V				
		SIZE: A3	DWG. NO.	OUTLINE OL-08075163	REV. A	
DO NOT SCALE DRAWING		SCALE 1:2			SHEET 1 OF 1	

