



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:  
 INTERRUPT RATING: 2000A @ 32VDC  
 VOLTAGE RATING: 32VDC  
 TEMP. RATING: -40°C - 125°C  
 CABLE TYPE: XLPE, SAE J1127, STX (4AWG), COLOR RED.  
 SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION  
 APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.  
 BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

**METRIC**  
ASSEMBLY

◀▶	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DUAL DIMENSIONS IN BRACKETS [ ] ARE INCHES AND FOR REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
●	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE.
CPK	CRITICAL CHARACTERISTIC FOR PART FIT/FUNCTION.
ST	CPK DIMENSION. 1.67 MINIMUM CPK VALUE ON NEW TOOLING. STATISTICAL PROCESS CONTROL DIMENSION. THIS DIMENSION INDICATES PROCESS PERFORMANCE. DATA SHALL BE TRACKED AND ANALYZED AT PERIODIC TIMES, ACC. TO CONTROL PLAN.
CP	CP DIMENSION. 1.67 MINIMUM CP VALUE. MUST BE INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.
Ⓞ	CUSTOMER-DESIGNATED CHARACTERISTIC. REQUIREMENT FOR EACH SYMBOL TO BE DEFINED IN A CONVERSION TABLE.
Ⓐ	CLAMP DIMENSION. PARTS SHALL BE SECURED BEFORE TAKING DIMENSIONAL MEASUREMENTS. FIXTURING DATUMS & PROCEDURES TO BE DEFINED IN NOTES OR SEPARATE PROCESS DOCUMENTS.

DIMENSIONS & TOLERANCES ACC. TO ASME Y14.5-2009	MATL SPEC	-	
	FINISH	-	
3RD ANGLE PROJECTION	DRW	TRG	CHK
SCALE FULL	DATE	02/08/05	
TOLERANCES UNLESS OTHERWISE SPECIFIED			
DIM	LINEAR DIMENSIONS		ANGLES
	UP TO .5	UP TO .6	UP TO 400
TOL	±0.1	±0.2	±0.5
TITLE CABLEPRO			
LTR		DATE	REVISION
A		02/08/05	61618 - RELEASED
B		3/3/05	842128-CHG 1240 TO 1195 & 1490 TO 1445.8
C		05/31/06	84765B-ADD NOTES FOR BAR CODE
D		22/APR/19	520732ECA-UPDATE TOLERANCE & DRAWING FORMAT
DRW		TRG	PJM
DRW		DHM	OPL
REVISION		DRWG. NO.	OUTLINE
D		0L-0496200.ZXW	
LITTELFUSE		CHICAGO, USA 773-628-1000	