



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
- VOLTAGE RATING: 32VDC
- TEMP. RATING: -40°C - 125°C
- CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
- SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
- APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
- BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	FINISH	
1	9	18	DRW	DATE 07/13/05
2	10	19	MTS	SCALE FULL
3	12	20	CHK	DATE SUPER DRW
4	13	21	APPD	DATE FINISH GOOD WT
5	14	23	APPD	DATE GRAMS/PIECE
6	15	33		TOLERANCE UNLESS OTHERWISE SPECIFIED
7	16	43		TWO PLACE DEC ±.25[.01] FRACTION ±
8	17	53		THREE PLACE DEC ±.100[.004] ANGULAR ±1°
3RD ANGLE PROJECTION		TITLE		
		CABLEPRO		
LTR		REVISION		CHK
A	61766	- RELEASED	7/18/05	MTS
B	84765B-CODE	ADD NOTES	05/31/06	FOR BAR DHM

REVISION	DRWG. NO.	OUTLINE
B	0496200	.ZXY

Littelfuse
DES PLAINES, ILLINOIS 60016

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT MUST BE WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE LITTELFUSE PRODUCT INSTRUCTIONS.
 DENOTES CP DIMENSIONS, -MINIMUM CP VALUE
 DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE LITTELFUSE PRODUCT INSTRUCTIONS AND FOR MAXIMUM TOOL LIFE.

