





REV.		DESCRIPTION	DATE	DESIGNED	APPROVED
A		FIRST ISSUE OF OUTLINE DRAWING	15-June-20	Gasparini	Tinto




Scale 1:2



Markinh showing:
-Code IVECO
-Code LITTELFUSE
-Manufacturing date
according to
LITTELFUSE standard

-Code IVECO
-LITTELFUSE
production progressive
code

Connector DIN 72585-A1-7 ways



PRESCRIPTIONS:

- Torque of screw M10= 19Nm max
- Fix the device with M6 screws and with torque of 6 ± 2 Nm
- Nuts and bolts supplied on the kit LITTELFUSE code 10844041

CHARACTERISTICS:

- Nominal working tension: 11 - 28.5 V
- Nominal working current: 10A
- Nominal working current main contacts: 500 A (1h at 23°C)
- Nominal max current main contact: 2000A for 5 sec
- External emergency switch - LITTELFUSE code 00227000

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10 50	>50 120	>120 400	>400 1000	>1000 2000	>2000 4000
±1°30'	±1°	±0°30'	±0°15'	±0°15'	±0°15'	±0°15'
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
	NAME	DATE	 Expertise Applied Answers Delivered			
DRAWN	L. Del Molin	07/05/2019				
CHECKED	-	-				
			TITLE			
			Electrical BDS			
			FORM NO. CVP-PE40-0013 REV A			
			FIRST ANGLE PROJECTION			
			SIZE: A2			
			DWG. NO. OL-08075161			
			OUTLINE REV. A			
			DO NOT SCALE DRAWING			
			SCALE 1:1			
			SHEET 1 OF 1			