

PART NUMBER	FIGURE	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	INSULATION TYPE	WIRE SIZE	RATING MARK	PKG QTY
OFHJ1001G	1	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	10 AWG	40A	250
OFHJ1002G	1	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	250
OFHJ1002L	1	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	50
OFHJ2001G	2	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	10 AWG	40A	250
OFHJ2002G	2	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	250
OFHJ2002L	2	102.0±5.0	102.0±5.0	9.0±2.0	9.0±2.0	RED	RED	GXL (STANDARD)	8 AWG	60A	50

- NOTES:
- HOLDER MATERIAL: BLACK TPV MATERIAL
 - CONTACTS: TIN-PLATED COPPER ALLOY
 - WIRE SIZE & LENGTH: SEE CHART
 - MAX TEMPERATURE: 125° C
 - RATING MARKING: SEE CHART
 - FUSE HOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION.
 - ALL PARTS PACKAGED BULK IN QTY SHOWN.

LTR	DATE	REVISION	CHK	APD
A	11/19/09	000847ER-RELEASED CAD		
B	08/17/12	505869ECA-REMOVAL OF MOUNTING HOLE OPL		
C	04/16/15	511793ECA-COMPILED ALL OFHJ HOLDERS ONTO ONE PRINT; ADDED PKG NOTES; ADDED BRACKET VERSION VIEWS; PRINT NAME CHANGED FROM OFHJ1000G TO OFHJ00000. FYUE		








FIGURE 1. STANDARD HOLDER



RATING MARKING (SEE CHART)

FIGURE 2. HOLDER WITH MOUNTING BRACKET



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES						
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.						
	DENOTES CRITICAL CHARACTERISTICS.					
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
COPIES TO		MATL SPEC				
1	9	18	FINISH			
2	10	19				
3	12	20				
4	13	21				
5	14	23				
6	15	33				
7	16	43				
8	17	53				
DRW		CAD		DATE	11/19/09	SCALE
CHK		DATE		SUPER DR		
APPD		DATE		FINISH GOOD WT		
GRAMS/PIECE						
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)						
DIMENSION	0.5 - 3	UP TO 3 OVER 3 - 6	UP TO 6 OVER 6 - 30	UP TO 30 OVER 30 - 120	UP TO 120 OVER 120 - 400	UP TO 400 OVER 400 - 1000
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.7
3RD ANGLE PROJECTION 		TITLE				
		INLINE JCASE HOLDER WITHOUT COVER				
		REVISION		DRWG. NO.		OUTLINE
DES PLAINES, ILLINOIS 60016		C		OL-OFHJ00000		

METRIC
ASSEMBLY

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED