







PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	LEAD "A" SIZE	LEAD "B" SIZE	LEAD "A" STRIP	LEAD "B" STRIP	INSULATION TYPE
OFHM0003ZXJC-F10	329.7±5 [12.98±0.2]	79.8±5 [3.14±0.2]	12.7±2 [.50±0.08]	6.35±2 [.25±0.08]	BLACK	BLACK	16 AWG	16 AWG	PARTIAL	PARTIAL	GXL

LTR	DATE	REVISION	CHK	APD
A	06/01/15	514355GCA-RELEASED FYUE		



IN-LINE FUSEHOLDER WITH
10A MINI FUSE INSTALLED

- NOTES:
- HOLDER MATERIAL: BLACK TPV
 - CONTACTS: COPPER ALLOY: TIN-PLATED
 - WIRE: STRANDED COPPER, 125°C RATED, GXL/TXL WIRE (SEE CHART FOR WIRE SIZE)
 - CRIMP: MUST MEET SAE/USCAR 21 STANDARD
 - RATING: 10A, 32Vdc
 - MAX TEMPERATURE 125°C

METRIC

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
⊙	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
⬢ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
COPIES TO		MATL SPEC	
1 9 18		SEE NOTES	
2 10 19		FINISH	
3 12 20		SEE NOTES	
4 13 21		DRW FYUE	DATE 06/01/15
5 14 23		SCALE 1:1	
6 15 33		CHK	DATE
7 16 43		SUPER DR	
8 17 53		APPD	DATE
		FINSH GOOD WT	GRAMS/PIECE
TOLERANCE UNLESS OTHERWISE SPECIFIED ONE PLACE DEC +/- .3 THREE PLACE DEC +/- .100 TWO PLACE DEC +/- .15 ANGULAR +/- 1°			
3RD ANGLE PROJECTION			
TITLE MINI IN-LINE FUSEHOLDER WITH 10A FUSE			
Littelfuse		REVISION A	DRWG. NO. OFHM0003ZXJC-F10
DES PLAINES, ILLINOIS 60016		OUTLINE	

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED