






PART NUMBER	WITH BOX
OFHZ0005Z	NONE
OFHZ0005Z-BX	CA-606



NOTES:

1. MATERIALS:
BASE/COVER: BLACK FR530
BUS BAR: C1100 Sn PLATED
TETHER: BLACK SILICON RUBBER
DUST COVER: GREEN SILICON RUBBER
STUD: STEEL Zn/Fe ALLOY PLATED
BOTTOM CAP: BLUE PA66
LATCH: YELLOW POM
FLANGE NUT: STAINLESS STEEL
2. MAX. MAIN INPUT: 400A
3. OPERATING TEMPERATURE RANGE: -40° C TO 85° C
4. M5 MOUNTING TORQUE: 10±2 Nm
5. MAX. WIRE SIZE 105 sqmm OR AWG 4/0.



LTR	DATE	REVISION	CHK	APD
A	26/Jun/18	519497GCC-NEW RELEASE	FYUE	

9	873-716	COVER	1	EA
8	883-088	LATCH	2	EA
7	980003760	MB NUT	5	EA
6	901-520	DUST COVER	5	EA
5	882-869-5	BUS BAR	1	EA
4	890009470	TETHER	1	EA
3	868-967	BASE	1	EA
2	908-067	MB STUD	5	EA
1	883-094	BOTTOM CAP	2	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS () ARE INCHES.				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO		MATE SPEC		
1	9	18	SEE NOTE	
2	10	19	FINISH	
3	12	20	SEE NOTE	
4	13	21	DRW	FYUE
5	14	23	DATE	26/Jun/18
6	15	33	CHK	DATE
7	16	43	APPD	DATE
8	17	53	FINSH	GOOD WT
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF: ISO 2768-TH)		GRAMS/PIEC		
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	±0.1	±0.1	±0.2	±0.3
3RD ANGLE PROJECTION				
TITLE		UNSEALED 4-WAY ZCASE FUSE BOX		
METRIC ASSEMBLY				
LITTELFUSE				
DES PLAINES, ILLINOIS 60014				
REVISION		DRWG. NO.		OUTLINE
A		OFHZ0005Z		

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED