







REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	520253GCC-NEW RELEASE DRAWING	21/May/19	



SECTION A-A



NOTES:

- MATERIALS:
BASE/COVER: PET WITH GF (UL-94V0)
BUS BAR: COPPER Sn PLATED
STUD: STEEL Ni/Fe ALLOY PLATED
BOTTOM CAP: PA66
LATCH: POM
- MAX. MAIN INPUT: 400A
- OPERATING TEMPERATURE RANGE: -40°C TO 85°C
- M8 MOUNTING TORQUE: 12-15 Nm
- MAX. WIRE SIZE 105 sqmm OR AWG 4/0

6	873-723	COVER	1	EA
5	883-088	LATCH	2	EA
4	882-869-7	BUS BAR	1	EA
3	868-994	BASE	1	EA
2	908-067	M8 STUD	7	EA
1	883-097	BOTTOM CAP	2	EA
NO.	COMPONENT NO.	COMPONENT NAME	QTY/M	U/M

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

●	DENOTES PRODUCTS CRITICAL CHARACTERISTICS
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

TOLERANCES UNLESS OTHERWISE SPECIFIED
ONE PLACE DECIMAL ± 0.5
TWO PLACES DECIMAL ± 0.20
THREE PLACES DECIMAL ± 0.100
ANGULAR ± 2°

NAME		DATE			Littelfuse®	
DRAWN	FRANK YUE		26/Dec/18			
CHECKED						
THIRD ANGLE PROJECTION			TITLE			
			UNSEALED 6-WAY ZCASE FUSE BOX			
DO NOT SCALE DRAWING			SIZE	DWG. NO.	REV.	
			C	OL-0FHZ0006Z	A	
			SCALE 1:2		SHEET 1 OF 1	