







REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	520253GCC-NEW RELEASE DRAWING	23/May/19	



SECTION A-A



NOTES:

- MATERIALS:
BASE/COVER: PET WITH GF (UL-94V0)
BOTTOM CAP: PA66
LATCH: POM
- MAX. MAIN INPUT: 400A
- OPERATING TEMPERATURE RANGE: -40 °C TO 85 °C
- M8 MOUNTING TORQUE: 12-15 Nm
- MAX. WIRE SIZE 105 sqmm OR AWG 4/0

4	873-723	COVER	1	EA
3	883-088	LATCH	2	EA
2	868-994	BASE	1	EA
1	883-097	BOTTOM CAP	2	EA
NO.	COMPONENT NO.	COMPONENT NAME	QTY/M	U/M

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.				
	DENOTES PRODUCTS CRITICAL CHARACTERISTICS			
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°				
NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered		
DRAWN	FRANK YUE			
CHECKED	-			
-	-			
-	-	TITLE		
-	-			
THIRD ANGLE PROJECTION		UNSEALED 6-WAY ZCASE FUSE BOX		
		SIZE	DWG. NO.	REV.
DO NOT SCALE DRAWING		C	OL-0FHZ0008Z	A
SCALE 1:2			SHEET 1 OF 1	