



PART No.	BODY	BODY STYLE	FUSE PROVIDED	FUSE RATING	REMARKS
OFNY0001Z	OFNY0001Z	1	NONE	----	NOTE 1
OFNY0004Z	OFNY0001Z	1	0307004.Z	4 AMP	NOTE 1
OFNY0006Z	OFNY0001Z	1	0307006.Z	6 AMP	NOTE 1
OFNY00075Z	OFNY0001Z	1	0307007.5Z	7.5 AMP	NOTE 1
OFNY0009Z	OFNY0001Z	1	0307009.Z	9 AMP	NOTE 1
OFNY0014Z	OFNY0001Z	1	0307014.Z	14 AMP	NOTE 1
OFNY0020Z	OFNY0001Z	1	0307020.Z	20 AMP	NOTE 1
OFNY0030Z	OFNY0030Z	2	0307030.Z	30 AMP	NOTE 2

OBS.
OBS.

BODY STYLE #1



BODY STYLE #2

NOTES:

1. FOR OFNY0001:

- A) MAX. RATING: 20 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 180° F (82° C).
- B) BODY MATERIAL: NYLON 6/6, BLACK
KNOB MATERIAL: NYLON 6/6, BLACK
SPRING MATERIAL: COATED STEEL
CONTACT RIVET MATERIAL: BRASS
WIRE LEAD MATERIAL: #14 GAUGE, STRANDED, BLACK
- C) FUSEHOLDER IS SHIPPED WITH KNOB AND BODY ASSEMBLED (FUSE INSTALLED, IF REQUIRED) FORMING A LOOP.

2. FOR OFNY0030:

- A) MAX. RATING: 30 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 180° F (82° C).
- B) BODY MATERIAL: NYLON, WHITE TRANSLUCENT
KNOB MATERIAL: NYLON 6/6, BLACK
SPRING MATERIAL: COATED STEEL
CONTACT RIVET MATERIAL: BRASS
WIRE LEAD MATERIAL: #12 GAUGE, STRANDED, ORANGE PVC, G.P. SAE TYPE 1
- C) FUSEHOLDER IS SHIPPED WITH KNOB AND BODY ASSEMBLED (FUSE INSTALLED).

GENERAL NOTES:

- 1. TOTAL WEIGHT OF SHIPPING CARTON SHALL BE LIMITED TO 50 LBS. MAX.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
MATERIAL SPEC		FINISH	SCALE 1=1	
COPIES TO	DATE	JMB	DATE	SUPER DRW
1 9 18	2/11/99			
2 10 19				
3 12 20				
4 13 21				
5 14 23				
6 15 33				
7 16 43				
8 17 53				
TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.01 THREE PLACE DEC ±.005 ANGULAR ±1°				
FUSEHOLDER, IN LINE (FUSE OPTIONAL)				
DRAWING NO. SERIES OUTLINE OFNY0000Z				
G				

REVISION

LTR

CHK

APD

F

G

-

3/21/03

BJJ

39728C- REVISE & REDRAWN
ON NEW FORMAT 2/26/99 JMB82904C - OBS. OFNY0075Z,
OFNY0009Z

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. REFERENCE THE INSTRUCTIONS FOR MEASUREMENT AND INSPECTION INSTRUCTIONS.

DENOTES CP DIMENSIONS.-MINIMUM CP VALUE
CPK VALUE WITHIN THE DIMENSIONAL LIMITATIONS
AND MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT