

LTR	DATE	REVISION		CHK	APD
A	6/27/13	508692ERA-RELEASED	FYUE		




FIGURE 1. M8 STUD CAP

PART #	BASE PART	DESCRIPTION	FIGURE
09230025LXRED	923-025-001	STUD CAP-3/8" RED	2
09230025LXBLK	923-025-002	STUD CAP-3/8" BLACK	2
09230025LXREDM8	923-025-003	STUD CAP-M8 RED	1
09230025LXBLKM8	923-025-004	STUD CAP-M8 BLACK	1





FIGURE 2. 3/8" STUD CAP

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
				
COPIES TO		MATL SPEC		
		SILICONE		
1 9 18	FINISH			
2 10 19	SEE CHART FOR COLOR			
3 12 20				
4 13 21	DRW	FYUE	DATE	SCALE
5 14 23			06/27/13	1:1
6 15 33	CHK		DATE	SUPER DR
7 16 43	APPD		DATE	FINSH GOOD WT
8 17 53	GRAMS/PIECE			
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)				
DIMENSION	0.5 - 3	UP TO 3	OVER 3 - 6	UP TO 6
TOLERANCE	+0.05	+0.05	+0.1	+0.15
				+0.2
3RD ANGLE PROJECTION	TITLE			
	STUD CAPS			
		REVISION	DRWG. NO.	OUTLINE
CHICAGO, USA 773-628-1000		A	OL-09230025LX	SERIES

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)