







LTR	DATE	REVISION	CHK	APD
A	04/24/15	GCF511823GCA-NEW RELEASE FYUE		



-				
-				
-				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
				
COPIES TO		MATL SPEC COVER: THERMOPLAST HOLDER: THERMOPLAST DFK2 CONTACTS: COPPER ALLOY		
1	9	18	FINISH	
2	10	19	-	
3	12	20		
4	13	21	DRW	FYUE
5	14	23	DATE	04/24/15
6	15	33	SCALE	4:1
7	16	43	CHK	DATE
8	17	53	SUPER DR	
			APPD	DATE
			FINSH GOOD WT	
GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)				
DIMENSION	0.5	UP TO 3	OVER 3 - 6	UP TO 6
			OVER 6 - 30	UP TO 30
			OVER 30 - 120	UP TO 120
			OVER 120 - 400	UP TO 400
TOLERANCE	±0.1	±0.1	±0.2	±0.3
			±0.3	±0.5
3RD ANGLE PROJECTION	TITLE			
	FH2 HOLDER WITH BLADE TERMINAL			
			REVISION	DRWG. NO.
CHICAGO, USA 773-628-1000			A	178.6105.1002
			OUTLINE	

METRIC
ASSEMBLY

Littelfuse
CHICAGO, USA 773-628-1000

REVISION
A

DRWG. NO.
178.6105.1002

OUTLINE

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)