






PART NUMBER	WITH BOX
0FHZ0002Z	NONE
0FHZ0002Z-BX	CA-606



NOTES:

1. MATERIALS:
 BASE/COVER: BLACK FR530
 BUS BAR: C100 Sn PLATED
 TETHER: BLACK SILICON RUBBER
 DUST COVER: GREEN SILICON RUBBER
 STUD: STEEL Zn/Pb ALLOY PLATED
 BOTTOM CAP: BLUE PA66
 LATCH: YELLOW POM
 FLANGE NUT: STAINLESS STEEL
2. MAX. MAIN INPUT: 400A
 OPER. TEMPERATURE RANGE: -40°C TO 85°C
 MB MOUNTING TORQUE: 0.22 Nm
 MAX. WIRE SIZE 105 sqmm OR AWG 4/0.

[illegible]

11	873-716	COVER	1	EA
10	883-088	LATCH	2	EA
9	980003760	MB NUT	4	EA
8	890000670	M10 NUT	1	EA
7	901-520	DUST COVER	5	EA
6	882-869-5	BUS BAR	1	EA
5	8900009470	TETHER	1	EA
4	868-967	BASE	1	EA
3	908-067	MB STUD	4	EA
2	908-068	M10 STUD	1	EA
1	883-094	BOTTOM CAP	2	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.

DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED
	LITTLEFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

COPIES TO			MAT. SPEC		SEE NOTE					
1	9	18	FINISH							
2	10	19								
3	12	20	SEE NOTE							
4	13	21	DRW		FYVE		DATE	26/Jun/18	SCALE	1:1
5	14	23	CHK				DATE		SUPER DR	
6	15	33								
7	16	43	APPD				DATE		FINISH GOOD WT	
8	17	53								
GRAMS/PIECE										

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-PM)					
DIMENSION	0.5 UP TO 3	OVER 3 UP TO 6	OVER 6 UP TO 30	OVER 30 UP TO 120	OVER 120 UP TO 400
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5

	TITLE UNSEALED 4-WAY ZCASE FUSE BOX		
 DES PLAINES, ILLINOIS 60016	REVISION A	DRWG. NO. OFHZ0002Z	OUTLINE

CAD GENERATED DRAWING – NO PENCIL CHANGES ALLOWED