





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.


REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300031. INITIAL RELEASE. DSILVA	3/7/2022	S.CASTILLO



- NOTES:
- MATERIAL:
 - BATTERY TERMINAL: COPPER ALLOY, TIN PLATED.
- ☒ DYNAMIC TORQUE: 5.4Nm±0.9Nm @ 540 RPM MAX

BOM			
ITEM	DESCRIPTION	QTY	UM
1	BATTERY TERMINAL	1	EA
2	M6 CARRAGE BOLT	1	EA
3	M6 FLANGE NUT	1	EA

DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°			
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.			
PER CHNFPD20-008 PROCEDURE	●	FIT/ FUNCTION CRITICAL CHARACTERISTICS	
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL	
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE	
	(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS	
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE	

		NAME	DATE
DRAWN		DSILVA	2/28/2022
CHECKED		S.CASTILLO	3/7/2022
		-	-
		-	-
FORM NO. CVP-PE40-0005 REV B			
THIRD ANGLE PROJECTION			
			
DO NOT SCALE DRAWING			

		Littelfuse®	
Expertise Applied Answers Delivered			
TITLE			
TERMINAL ASSEMBLY-BMZ			
SIZE	DWG. NO.	OL-0FHZ00852	REV. A
C	OUTLINE		
SCALE 1:2		SHEET 1 OF 1	