


Toggle Switches

55025 Sealed



Description

Littelfuse Toggle Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

The 55025 series is our most popular sealed toggle switch product, meant to be mounted in virtually any environment and for any application.

Web Resources

Download 2D print and technical resources at:
littelfuse.com/55025

Ordering Information

PART NUMBER	POSITIONS	CIRCUITRY
55025	On-Off	SPST (Hardware Assembled)
55025-01	Mom. On-Off	SPST
55025-02	On-Off-On	SPDT
55025-03	On-On	SPDT
55025-04	Mom. On-Off-Mom. On	SPDT
55026	On-Off	DPST

Specifications Overview

Voltage Rating:	25A @ 12V DC 15A @ 24V DC
Circuitry:	SPST
Housing:	Black Plastic
Operating Temperature:	-40°C to 85°C
Mounting:	Nickel Plated Brass Face Nut through 15/32 (11.90mm) Panel Hole
Ingress Protection:	IP67
Actuator:	Standard handle: 11/16" (17.46mm) long
Termination:	2 blunt-cut 14AWG leads

Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

Features and Benefits

- Application sealed through actuator O-Ring and epoxy-sealed connection interface
- Silver contacts for corrosion resistance