




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.		
ART. NR.	DESCRIPTION	NOTE
178.6105.0001	FH2 BLOCK HOLDER PKG 100 PCS	-
178.6105.0002	FH2 BLOCK HOLDER BULK 1000 PCS	-

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300044. INITIAL RELEASED. DSILVA.	4/21/2022	L.ARGIL

- NOTES:
- MATERIAL
 - COVER: THERMOPLASTIC
 - HOLDER: THERMOPLASTIC
 - DFK CONTACTS: COPPER ALLOY

3	-	HOUSING				1000	EAD
2	-	COVER				1000	EAD
1	-	DFK2 CONTACTS				2000	EAD
NO.		COMPONENT NO.				COMPONENT NAME	QTY U
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)							
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400			ANGLE
±0.10	±0.10	±0.20	±0.30	±0.50			NONE
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.							
PER CHNFPD20-008 PROCEDURE	● FIT/ FUNCTION CRITICAL CHARACTERISTICS						
	<S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL						
	CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE						
	(ST) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS						
	CP DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE						
DRAWN		NAME		DATE		 Littelfuse Expertise Applied Answers Delivered TITLE FH2 - BLOCKHOLDER, COMPLETE SIZE C DWG. NO. OUTLINE OL-178.6105.0000 REV. A DO NOT SCALE DRAWING SCALE 2:1 SHEET 1 OF 1	
CHECKED		DSILVA		4/13/2022			
		-		-			
		-		-			
		-		-			
FORM NO. CVP-PE40-0005 REV B							
THIRD ANGLE PROJECTION							
