





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

276.5105.5252	KABELVERBINDER ATS/OTS (25 A ATS FUSE)
276.5105.5162	KABELVERBINDER ATS/OTS (16 A ATS FUSE)
276.5105.4803	KABELVERBINDER ATS/OTS (8 A ATS FUSE)
276.5105.4802	KABELVERBINDER ATS/OTS (8 A ATS FUSE)
276.5105.4502	KABELVERBINDER ATS/OTS (5 A ATS FUSE)
276.5105.0000	KABELVERBINDER ATS/OTS (WITH OUT FUSE)
PART NUMBER	DESCRIPTION
CHART	

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	ECR 524363 CAD DRAW REALISE. -E. FLORES	11/18/2021	S. CASTILLO



- NOTES:**
- 1.- ALL DIMENSIONS ARE REFERENCE
 - 2.- DIMENSIONS UNIT: mm
 - 3.- 3D FILE ONLY USED FOR REFERANCE PURPOSES.

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

●	FIT/ FUNCTION CRITICAL CHARACTERISTICS
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

PER CHI-NPD20-0008 PROCEDURE

NAME	DATE
DRAWN E. FLORES	11/18/2021
CHECKED S. CASTILLO	11/18/2021
-	-
-	-

Littelfuse
Expertise Applied | Answers Delivered

FORM NO: CVP-PE40-0003 REV B
THIRD ANGLE PROJECTION

TITLE **KABELVERBINDER ATS/OTS**

SIZE B	DWG. NO. OL-276.5105.0000,CHART	REV. A
DO NOT SCALE DRAWING	SCALE 2:1	SHEET 1 OF 1