






LTR	DATE	REVISION	CHK	APD
A	08/02/13	509148ERA-REDRAWN IN UG FYUE		
B	11/Jul/16	516095ECA-REMOVE MATERIAL SUPPLIER MODEL NUMBER FYUE		

INSPECTION NOTES:
1. INSPECT STRIPPED WIRE FOR CUT STRANDS
(CONFORMS WITH IPC-A-610 STD.)
2. NO DAMAGE TO WIRE INSULATION
3. NO SHORT SHOTS ON MOLDING
4. FLASH OR GATING NOT TO EXCEED 0.13


NOTES:
1. HOLDER MATERIAL: BLACK TPV
2. CONTACTS: C2680 BRASS TIN-PLATED
3. WIRE: PVC FLY HT105° RED ISO 6722 SEC. 2.5mm²
4. CRIMP: MUST MEET SAE/USCAR 21 STANDARD
5. RATING: MAX. 20A, 32Vdc
6. MAX TEMPERATURE: 105° C
7. SHIPPED WITH COVER IN OPEN POSITION




DETAIL A
SCALE 2:1



SECTION B-B



IN-LINE FUSEHOLDER SHOWN
WITH ATO FUSE INSTALLED
(COVER NOT SHOWN)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
COPIES TO		MATL SPEC	
		SEE NOTES	
1 9 18	FINISH		
2 10 19	SEE NOTES		
3 12 20			
4 13 21	DRW FYUE	DATE 08/02/13	SCALE 1:1
5 14 23	CHK	DATE	SUPER DR
6 15 33	APPD	DATE	FINISH GOOD WT
7 16 43	GRAMS/PIECE		
8 17 53			
TOLERANCE UNLESS OTHERWISE SPECIFIED			
ONE PLACE DEC +/- .3		THREE PLACE DEC +/- .100	
TWO PLACE DEC +/- .25		ANGULAR +/- 1°	
3RD ANGLE PROJECTION	TITLE		
	ATO IN-LINE FUSEHOLDER		
		REVISION B	DRWG. NO. 277.6306.0001
DES PLAINES, ILLINOIS 60016		FINAL	

METRIC