

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ASSOCIATED CAD FILE DEFINES ALL NONDIMENSIONED FEATURES

2. PRODUCT WEIGHT: 0.22 Kg

3. MAXIMUM TERMINAL STUD TORQUE: 13.56 NM (120IN-LB)

4. PAD LOCK HOLE FOR LOCKOUT IN OFF POSITION

5. FRONT PANEL MOUNT IN 67MM (2-5/8") HOLE

6. TERMINAL HARDWARE 1: 3/8"-16 NUT SERRATED FLANGE, STAINLESS STEEL






7. METALLIC LABEL: LABEL INFORMATION TO CONSIST OF:
o COOPER BUSSMANN P/N: MSW-300-32-S-BLO
o LITTELFUSE P/N: 880064100
o SERIAL NUMBER
o BARCODE

8. TERMINAL HARDWARE 2: SPACER, 110 COPPER

9. ELECTRICAL SPECIFICATOIN:
- MAX OPERATING VOLTAGE: 32V DC
- MAX CONTINUOUS CURRENT: 300A
- CRANKING RATING (30 SEC) (1X4/0 CABLE): 1,250A

10. INGRESS RATING: IP67 & IP69K

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	INITIAL RELEASE	2/4/2014	D. RIEL
	B	PER EC# 509798 REV CHANGE	2/27/2014	D. RIEL
	C	PER EC#511645: INVERTED TEXT, REDUCED KNOB STOPPER HEIGHT, MODIFIED RING LABEL, ADDED WASHERS TO THE TERMINAL STUDS	11/12/2014	J. LIU
	D	PER EC#515935: ADDED A PERPENDICULARITY CALLOUT	5/26/2016	J. LIU



DIMENSIONS ARE IN MM.		DRAWN		NAME	DATE
DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI / ASME Y14.5M-1994		J. Liu			01/22/2014
THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.		CHECKED		-	-
		-		-	-
		-		-	-
		-		-	-
		THIRD ANGLE PROJECTION			
		SIZE		DWG. NO.	REV.
		C		OL-880064100	D
		SCALE 1:1		SHEET 1 OF 1	



805 W ORCHARD DR., STE 6, BELLINGHAM, WA 98226
Phone (360)738-9010 Fax (360)738-0372

Switch Master Panel Mount LO CB
Part Number: 880064100