





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO#5300103. INITIAL RELEASE. DSILVA.	10/4/2022	L.ARGIL



SCALE 1:1



SECTION B-B

- NOTES:
- THE 3D MODEL OF THIS PART IS TO BE USED AS A REFERENCE ONLY.
 - MATERIAL: NYLON POLYAMIDE, COLOR BLUE.

NO.	COMPONENT NO.	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M) FOR METAL, REF SPI PLASTICS				
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400
±0.10	±0.10	±0.20	±0.30	±0.50
				ANGLE
				±0.5°
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.				
PER CH1-NPD20-0008 PROCEDURE	●	FIT/ FUNCTION CRITICAL CHARACTERISTICS		
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL		
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE		
	ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
	NAME	DATE	Littelfuse Expertise Applied Answers Delivered TITLE TPA	
DRAWN	DSILVA	7/19/2022		
CHECKED	-	-		
	-	-		
FORM NO: CVP-PE40-0003 REV B				
THIRD ANGLE PROJECTION				
			SIZE B	DWG. NO. OUTLINE
DO NOT SCALE DRAWING			SCALE 2:1	REV. A
			SHEET 1 OF 1	