



NOTE:

1. MATERIAL: NYLON66 - BLUE
2. OPERATING & STORAGE TEMPERATURE: -40 °C TO 85 °C
3. ALL DIMENSIONS SHOWN FOR REFERENCE ONLY
4. (3) TPA'S ARE REQUIRED PER HWB18 FUSE MODULE
5. TPA'S ARE INSTALLED TO HWB18 BASE AFTER WIRES WITH DELPHI TERMINALS AND SEALS ARE INSTALLED

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
Ⓞ		DENOTES CRITICAL CHARACTERISTICS.		
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		

LTR	DATE	REVISION	CHK	APD
A	04/24/12	504798ERA - INITIAL RELEASE FYUE		
B	05/18/12	504988ECA - ADDED ERN NUMBER TO REVISION A FYUE		

COPIES TO	MATL SPEC				REFER TO NOTE 1					
1	9	18			FINISH					
2	10	19			SCALE					
3	12	20			DRW	FYUE	DATE	04/24/12	SCALE	2:1
4	13	21			CHK		DATE		SUPER DR	
5	14	23			APPD		DATE		FINISH GOOD WT	
6	15	33			TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)					
7	16	43			DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400
8	17	53			TOLERANCE	±0.05	±0.05	±0.1	±0.15	±0.2
3RD ANGLE PROJECTION										
TITLE TPA OUTLINE (HWB18)										
REVISION DRWG. NO.										
B OL-883-084										

